

# DIN RAIL FUSE HOLDERS



**ASK Fuse Holder Series Starts at \$4.25**



ASK-4-31, \$28, shown larger than actual size.

- DIN Rail Mounted Fuse Holders
- 1, 2, and 3-Pole
- Models With Blown Fuse Indication
- 600V, 32 A (ASK 4)
- 600V, 50 A (ASK 6)

The ASK Series of DIN rail mounted fuse holders provides circuit protection for any industrial control system. Two standard fuse styles are supported: 14 x 51 mm (ASK 6) and 10 x 38 mm (ASK 4). Single pole, double pole, and 3 pole models are available, with or without blown fuse indicator lights. Fuses can be purchased separately (see accessories chart next page).

## TECHNICAL DATA—FUSE HOLDERS

### Maximum Operating Current:

ASK 4: 32A @ 600V

ASK 6: 50A @ 600V

Wire Range: 26–6 AWG

### Dimensions:

ASK 4 (1 pole): 17.5 W x 81 mm H (0.69 x 3.2")

ASK 6 (1 pole): 27 W x 94 mm H (1.06 x 3.7")

Standards: IEC 60947-1, IEC 60947-3



ASK-6-1, \$8, shown larger than actual size.

## To Order (Specify Model Number)

## MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	DESCRIPTION
ASK-4-1	\$4.25	DIN rail fuse holder, 10 x 38 mm (0.39 x 1.50") fuses, 1 pole, no indicator light
ASK-4-2	9.50	DIN rail fuse holder, 10 x 38 mm (0.39 x 1.50") fuses, 2 pole, no indicator light
ASK-4-3	15.00	DIN rail fuse holder, 10 x 38 mm (0.39 x 1.50") fuses, 3 pole, no indicator light
ASK-4-1I	8.25	DIN rail fuse holder, 10 x 38 mm (0.39 x 1.50") fuses, 1 pole, with indicator light
ASK-4-2I	18.00	DIN rail fuse holder, 10 x 38 mm (0.39 x 1.50") fuses, 2 pole, with indicator light
ASK-4-3I	28.00	DIN rail fuse holder, 10 x 38 mm (0.39 x 1.50") fuses, 3 pole, with indicator light
ASK-6-1	8.00	DIN rail fuse holder, 14 x 51 mm (0.55 x 2.01") fuses, 1 pole, no indicator light
ASK-6-2	15.00	DIN rail fuse holder, 14 x 51 mm (0.55 x 2.01") fuses, 2 pole, no indicator light
ASK-6-3	22.50	DIN rail fuse holder, 14 x 51 mm (0.55 x 2.01") fuses, 3 pole, no indicator light
ASK-6-1I	19.00	DIN rail fuse holder, 14 x 51 mm (0.55 x 2.01") fuses, 1 pole, with indicator light
ASK-6-2I	39.00	DIN rail fuse holder, 14 x 51 mm (0.55 x 2.01") fuses, 2 pole, with indicator light
ASK-6-3I	59.00	DIN rail fuse holder, 14 x 51 mm (0.55 x 2.01") fuses, 3 pole, with indicator light

Ordering Examples: ASK-4-1, DIN rail mount fuse holder for 10 x 38 mm (0.39 x 1.50") fuses, 1 pole, \$4.25.

ASK-6-3I, DIN rail mount fuse holder for 14 x 51 mm (0.55 x 2.01") fuses, 3 pole, with indicator light, \$59.



## ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
<b>DUAL ELEMENT 250V TIME DELAY FUSES FOR ASK6 SERIES</b>		
ECNR1-10PK	\$42.50	Fuses, 250V, 1 A, package of 10
ECNR2-10PK	40.50	Fuses, 250V, 2 A, package of 10
ECNR3-10PK	39.00	Fuses, 250V, 3 A, package of 10
ECNR5-10PK	37.00	Fuses, 250V, 5 A, package of 10
ECNR10-10PK	37.00	Fuses, 250V, 10 A, package of 10
ECNR15-10PK	30.00	Fuses, 250V, 15 A, package of 10
ECNR20-10PK	30.00	Fuses, 250V, 20 A, package of 10
ECNR25-10PK	30.00	Fuses, 250V, 25 A, package of 10
ECNR30-10PK	30.00	Fuses, 250V, 30 A, package of 10
<b>GENERAL PURPOSE 250V CLASS M TIME DELAY FUSES FOR ASK4 SERIES</b>		
MEN1-10PK	\$30.00	Fuses, 250V, 1 A, package of 10
MEN2-10PK	27.50	Fuses, 250V, 2 A, package of 10
MEN3-10PK	29.00	Fuses, 250V, 3 A, package of 10
MEN5-10PK	27.50	Fuses, 250V, 5 A, package of 10
MEN10-10PK	27.50	Fuses, 250V, 10 A, package of 10
MEN15-10PK	28.00	Fuses, 250V, 15 A, package of 10
MEN20-10PK	29.00	Fuses, 250V, 20 A, package of 10
MEN25-10PK	32.50	Fuses, 250V, 25 A, package of 10
MEN30-10PK	29.00	Fuses, 250V, 30 A, package of 10
<b>GENERAL PURPOSE 500V CLASS M TIME DELAY FUSES FOR ASK4 SERIES</b>		
MEQ1-10PK	\$79.00	Fuses, 500V, 1 A, package of 10
MEQ2-10PK	79.00	Fuses, 500V, 2 A, package of 10
MEQ3-10PK	79.00	Fuses, 500V, 3 A, package of 10
MEQ5-10PK	79.00	Fuses, 500V, 5 A, package of 10
MEQ10-10PK	79.00	Fuses, 500V, 10 A, package of 10
MEQ15-10PK	79.00	Fuses, 500V, 15 A, package of 10
MEQ20-10PK	79.00	Fuses, 500V, 20 A, package of 10
MEQ25-10PK	79.00	Fuses, 500V, 25 A, package of 10
MEQ30-10PK	79.00	Fuses, 500V, 30 A, package of 10
<b>FAST ACTING 600V CLASS CC FUSES FOR ASK4 SERIES</b>		
HCLR.5-10PK	\$76.00	Fuses, 600V, 0.5 A, package of 10
HCLR.75-10PK	83.00	Fuses, 600V, 0.75 A, package of 10
HCLR1-10PK	72.00	Fuses, 600V, 1 A, package of 10
HCLR1.5-10PK	72.00	Fuses, 600V, 1.5 A, package of 10
HCLR2-10PK	72.00	Fuses, 600V, 2 A, package of 10
HCLR2.5-10PK	93.00	Fuses, 600V, 2.5 A, package of 10
HCLR3-10PK	72.00	Fuses, 600V, 3 A, package of 10
HCLR3.5-10PK	97.00	Fuses, 600V, 3.5 A, package of 10
HCLR4-10PK	77.00	Fuses, 600V, 4 A, package of 10
HCLR5-10PK	72.00	Fuses, 600V, 5 A, package of 10
HCLR6-10PK	76.00	Fuses, 600V, 6 A, package of 10
HCLR7-10PK	88.00	Fuses, 600V, 7 A, package of 10
HCLR8-10PK	77.00	Fuses, 600V, 8 A, package of 10
HCLR9-10PK	97.00	Fuses, 600V, 9 A, package of 10
HCLR10-10PK	72.00	Fuses, 600V, 10 A, package of 10
HCLR12-10PK	73.00	Fuses, 600V, 12 A, package of 10
HCLR15-10PK	72.00	Fuses, 600V, 15 A, package of 10
HCLR20-10PK	72.00	Fuses, 600V, 20 A, package of 10
HCLR25-10PK	77.00	Fuses, 600V, 25 A, package of 10
HCLR30-10PK	72.00	Fuses, 600V, 30 A, package of 10

Note: For our entire selection of fuses visit [omegamation.com/fuse](http://omegamation.com/fuse)

M-X

ASK-6-1, \$19,  
shown larger  
than actual size.



ASK-4-1, \$4.25,  
shown larger  
than actual size.



MODEL NO.	PRICE	DESCRIPTION
<b>FAST ACTING 250V MIDGET CLASS FUSES FOR ASK4 SERIES</b>		
MOL5-10PK	\$21.00	Fuses, 250V, 0.5 A, package of 10
MOL1-10PK	16.75	Fuses, 250V, 1 A, package of 10
MOL1.5-10PK	21.00	Fuses, 250V, 1.5 A, package of 10
MOL2-10PK	16.75	Fuses, 250V, 2 A, package of 10
MOL2.5-10PK	21.00	Fuses, 250V, 2.5 A, package of 10
MOL3-10PK	16.75	Fuses, 250V, 3 A, package of 10
MOL4-10PK	21.00	Fuses, 250V, 4 A, package of 10
MOL5-10PK	16.75	Fuses, 250V, 5 A, package of 10
MOL6-10PK	16.75	Fuses, 250V, 6 A, package of 10
MOL8-10PK	17.00	Fuses, 250V, 8 A, package of 10
MOL10-10PK	15.00	Fuses, 250V, 10 A, package of 10
MOL15-10PK	15.00	Fuses, 250V, 15 A, package of 10
MOL20-10PK	17.00	Fuses, 250V, 20 A, package of 10
MOL25-10PK	19.00	Fuses, 250V, 25 A, package of 10
MOL30-10PK	17.00	Fuses, 250V, 30 A, package of 10
<b>FAST ACTING 600V MIDGET CLASS FUSES FOR ASK4 SERIES</b>		
MCL5-10PK	\$71.00	Fuses, 600V, 0.5 A, package of 10
MCL1-10PK	66.00	Fuses, 600V, 1 A, package of 10
MCL1.5-10PK	72.00	Fuses, 600V, 1.5 A, package of 10
MCL2-10PK	66.00	Fuses, 600V, 2 A, package of 10
MCL2.5-10PK	82.00	Fuses, 600V, 2.5 A, package of 10
MCL3-10PK	66.00	Fuses, 600V, 3 A, package of 10
MCL3.5-10PK	86.00	Fuses, 600V, 3.5 A, package of 10
MCL4-10PK	68.00	Fuses, 600V, 4 A, package of 10
MCL5-10PK	66.00	Fuses, 600V, 5 A, package of 10
MCL6-10PK	65.00	Fuses, 600V, 6 A, package of 10
MCL8-10PK	68.00	Fuses, 600V, 8 A, package of 10
MCL10-10PK	66.00	Fuses, 600V, 10 A, package of 10
MCL12-10PK	78.00	Fuses, 600V, 12 A, package of 10
MCL15-10PK	66.00	Fuses, 600V, 15 A, package of 10
MCL20-10PK	67.00	Fuses, 600V, 20 A, package of 10
MCL25-10PK	67.00	Fuses, 600V, 25 A, package of 10
MCL30-10PK	67.00	Fuses, 600V, 30 A, package of 10
<b>DIN RAIL</b>		
XBANS3575P	\$9.00	DIN rail, 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6'), slotted
XBANS3575U	9.30	DIN rail, 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6'), solid
XBANS3515P	17.00	DIN rail, 35 x 15 mm x 2 m (1.4 x 0.60" x 6.6'), slotted
XBANS3515U	17.00	DIN rail, 35 x 15 mm x 2 m (1.4 x 0.60" x 6.6'), solid
XBANS3575PL	15.00	DIN rail, 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6'), slotted, aluminum



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters