


DIN RAIL INTERFACE MODULES



**DSUB Series
Starts at
\$40**




* Male/female models only



DSUB-9-M, \$40, shown larger than actual size.

- D-Subminiature Connectors
- 9-, 15-, and 25-Pin Models
- Male, Female or Male/Female Connectors
- Optional D-SUB Cables Available
- 250 Vac Rated

The DSUB Series of DIN rail mounted interface modules provides a reliable “plug and play” interface for any industrial control system. Users can attach field wiring from the terminal blocks to their industrial control panel and then simply plug in their controller. These modules come with male, female or both male/female D-sub connectors for maximum flexibility.



DSUB-9-MF, \$58, shown larger than actual size.

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	DESCRIPTION	WIRE RANGE	MAX AMPS	LENGTH mm (in)	WIDTH mm (in)	HEIGHT mm (in)
DSUB-9-M	\$40	Interface module, 9-pin male	22-12	3	45 (1.77)	87 (3.43)	63 (2.5)
DSUB-9-F	40	Interface module, 9-pin female	22-12	3	45 (1.77)	87 (3.43)	63 (2.5)
DSUB-9-MF	58	Interface module, 9-pin male and female	22-14	1	39 (1.53)	93 (3.66)	63 (2.5)
DSUB-15-M	50	Interface module, 15-pin male	22-12	3	48 (1.89)	87 (3.43)	63 (2.5)
DSUB-15-F	50	Interface module, 15-pin female	22-12	3	48 (1.89)	87 (3.43)	63 (2.5)
DSUB-15-MF	68	Interface module, 15-pin male and female	22-14	1	49 (1.93)	93 (3.66)	63 (2.5)
DSUB-25-M	60	Interface module, 25-pin male	22-12	3	81 (3.19)	87 (3.43)	63 (2.5)
DSUB-25-F	60	Interface module, 25-pin female	22-12	3	81 (3.19)	87 (3.43)	63 (2.5)
DSUB-25-MF	88	Interface module, 25-pin male and female	22-14	1	73 (2.87)	93 (3.66)	63 (2.5)

CABLES

MODEL NO.	PRICE	DESCRIPTION
DSUB-9-MF-CBL	\$25	DSUB cable, 9-pin, 2 m (6.6'), male/female connectors
DSUB-15-MF-CBL	25	DSUB cable, 15-pin, 2 m (6.6'), male/female connectors
DSUB-25-MF-CBL	27	DSUB cable, 25-pin, 2 m (6.6'), male/female connectors

Comes complete with PIN identification.

Ordering Examples: DSUB-9-MF, DIN rail mount interface module, 9-pin with male/female, and DSUB-9-MF-CBL, DSUB cable, 9-pin, \$58 + 25 = \$83.

DSUB-15-M, DIN rail mount interface module, 15-pin with male, and DSUB-15-MF-CBL, DSUB cable, 15-pin, \$50 + 25 = \$75.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters