



THERMOCOUPLE TERMINAL BLOCKS

**XBTK Series
Starts at
\$8**



- Type J, K, T, E, R Terminal Blocks
- Screw Type Terminal Block DIN Connectors
- Maintenance-Free Connections
- Global Acceptance
- Large Surface Area for Marking

Thermocouple terminal blocks are offered in Type K, J, T, E and R. The terminal block contacts are made with thermocouple-grade calibration alloys. The terminal blocks come in a Gray color but white blank marker strips are available for identification.

SPECIFICATIONS

Terminal Width: 10.4 mm (0.41")
Maximum Wire Size: 12 AWG/2.5 mm²
Connection Data in V/AWG: 400/24-12
UL-cUL Ratings in V/AWG: 300/10/28-12
Width/Length/Cover Width in mm (in):
 5.2(0.20)/46.0(1.81)/1.0(0.04)
Height for 35 x 7.5/35 x 15 in mm (in):
 40.0(1.57)/47.5(1.87)/45.0(1.77)
Stripping Length in mm (in): 7 (0.28)
Thread: M3
Torque in (in-lb) Nm: 0.6 to 0.8 (5.3 to 7.1)

XBTKE25, \$8

Type **E**

XBTKJ25, \$8

Type **J**

XBTKK25, \$8

Type **K**

All models shown larger than actual size.

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
XBTKK25	\$8.00	Type K thermocouple terminal block
XBTKJ25	8.00	Type J thermocouple terminal block
XBTKE25	8.00	Type E thermocouple terminal block
XBTKT25	8.00	Type T thermocouple terminal block
XBTKR25	8.00	Type R thermocouple terminal block

MOST POPULAR MODELS HIGHLIGHTED!

Ordering Examples: XBTKK25, type K terminal block, XBACTK4-10PK, end covers, XBANS3575P, DIN rail, \$8 + 5.80 + 9 = \$22.80.
 XBTKJ25, (10 pcs.) type J terminal block, XBACTK4-10PK, end covers, XBMZB10-10PK, blank marker strip, XBANS3575P, DIN rail, (\$8 x 10) + \$5.80 + 4.60 + \$9.00 = \$99.40.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
XBACTK4-10PK	\$5.80	Gray end cover, pkg of 10
XBMZB10-10PK	4.60	White blank marker strip, pkg of 10
XBANS3575P	9.00	DIN rail 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6') slotted
XBANS3575U	9.30	DIN rail 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6.6') solid
XBANS3515P	17.00	DIN rail 35 x 15 mm x 2 m (1.4 x 0.60" x 6.6') slotted
XBANS3515U	17.00	DIN rail 35 x 15 mm x 2 m (1.4 x 0.60" x 6.6') slotted
XBAES35C-50PK	43.00	1-screw mounted end stop, pkg of 50
XBAES35T-50PK	32.00	3-screw mounted end stop, pkg of 50
XBAES35N-50PK	27.00	Snap-on end stop, pkg of 50



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters