

WATER-RESISTANT CONDUCTIVITY METERS

\$405
CDH-35




- ✓ Measure from 0.01 $\mu\text{S}/\text{cm}$ to 199.9 mS/cm with One Probe
- ✓ Ideal for Field Use – Water and Dust Resistant
- ✓ Low Battery System Prevents Erroneous Readings

This water-resistant, multi-range conductivity meter is recommended whenever measurements must be taken in the field. Even adverse weather conditions will not affect performance, as the housing resists both moisture and dust.

The CDH-35 is also one of the most versatile conductivity meters available, capable of measuring samples from deionized water to brine, using the same probe without recalibration. More accurate than amperometric probes, the 4-ring potentiometric probe is made of stainless steel for maximum protection in rugged conditions.

The meter also features automatic temperature compensation and a Battery Error Preventive System (BEPS) to alert the user when low batteries might affect results.



Environment:

0 to 50°C (32 to 122°F), 100% RH

Battery Type/Life:

9 V (alkaline battery)/100 hours of continuous use

Dimensions:

196 x 80 x 60 mm (7.7 x 3.1 x 2.4")

Weight:

425 g (15 oz); kit: 1.4 kg (3.1 lb)

SPECIFICATIONS

Range: 0.0 to 199.9 $\mu\text{S}/\text{cm}$,
0 to 1999 $\mu\text{S}/\text{cm}$, 0.00 to 19.99 mS/cm,
0.0 to 199.9 mS/cm

Resolution: 0.1 $\mu\text{S}/\text{cm}$, 1 $\mu\text{S}/\text{cm}$,
0.01 mS/cm, 0.1 mS/cm

Accuracy: 1% Full Scale

Calibration:

1 point through adjustment trimmer

Temperature Compensation:

Automatic from 10 to 40°C
(50 to 104°F) with a β of 2%/°C

To Order (Specify Model Number)		
Model No.	Price	Description
CDH-35	\$405	Water resistant conductivity meter, including 4-ring probe with 1 m (3') cable and hard plastic carrying case
CDE-35	142	4-ring probe with 1 m (3') cable (replacement)

Ordering Example: CDH-35, water resistant conductivity meter, including 4-ring probe with 1 m (3') cable and hard plastic carrying case, \$405.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters