


# LOW-FLOW LIQUID FLOWMETERS



FTB4705, \$230, shown smaller than actual size.



FTB4805, \$654, shown smaller than actual size.

FTB4700 Series Starts at

**\$230**



- ✓ Square-Wave Output
- ✓ One Moving Part
- ✓ Rugged, Nickel-Plated Brass Body or 316 SS

The FTB4700 Series comprises plated brass meters that are ideal for water applications, with ranges from 0.2 to 18 GPM. The FTB4800 covers a wide flow range and is housed in a rugged stainless steel package. Single-jet simplicity, combined with high-quality jewel bearings, results in long life and relatively high tolerance to harsh fluids. Typical applications include chemical batching, proportional chemical injection, fertilizer injection, proportioning of spray chemicals, and general flow rate monitoring.

The FTB4700 is available with 1/2 and 3/4" threads, with union-type meter couplings. The FTB4800 is available with 1/2, 3/4 and 1" threads. A square-wave output makes these meters ideal for many OEM control applications. This signal interfaces easily with programmable logic controllers and computer input boards. The FTB4700 or FTB4800 Series meters can be combined with the DPF701-A panel flow meter for reading flow rate or total flow, with 4 to 20 mA output.

## SPECIFICATIONS

Accuracy: ±1% FS

Maximum Temperature:

FTB4700: 85°C (185°F)

FTB4800: 93°C (200°F)

Maximum Pressure:

FTB4700: 12 bar (175 psi)

FTB4800: 35 bar (500 psi)

Output: Squarewave

Power:

FTB4700: 5 to 30 Vdc

FTB4800: 6 to 24 Vdc

Maximum Current: 20 mA

Cable: #22 AWG 3-conductor, 4 m (12')

Maximum Cable Run: 650 m (2000')

Maximum Pressure Drop: 15 psig

## Dimensions: mm (in)

Model No.	Overall Length	Height	Width
FTB4705	254 (10.0)	40 (1.56)	69 (2.7)
FTB4707	259 (10.2)	40 (1.56)	69 (2.7)
FTB4805	104 (4.1)	51 (2.0)	51 (2.0)
FTB4807	104 (4.1)	51 (2.0)	51 (2.0)
FTB4810	127 (5.0)	51 (2.0)	51 (2.0)

## Materials

	FTB4700	FTB4800
Body	Nickel-plated brass	316 SS
Rotor Chamber	Thermoplastic	Rotor cover: 316 SS
Rotor	Thermoplastic	PVDF
Shaft	Tungsten carbide	Nickel-bonded tungsten carbide
Bearings	Sapphire, graphite	Ruby ring and ball
O-Ring	—	TFE-coated FKM

**MOST POPULAR MODELS HIGHLIGHTED!**

## To Order (Specify Model Number)

Model No.	Price	K Factor (Pulses/Gal)	Description
FTB4705	\$230	308	1/2 MNPT, 0.2 to 10 GPM
FTB4707	237	174	3/4 MNPT, 0.2 to 18 GPM
FTB4805	654	560	1/2 FNPT, 0.1 to 10 GPM, 316 SS body
FTB4807	654	380	3/4 FNPT, 0.2 to 15 GPM, 316 SS body
FTB4810	654	168	1 FNPT, 0.5 to 25 GPM, 316 SS body

## Accessories

Model No.	Price	Description
DPF701	\$260	1/8" DIN panel meter, see page M-5 for complete details
CM-4339	135	Reference Book: Flow Measurement Methods and Applications

Comes complete with operator's manual.

Ordering Examples: FTB4705, 0.2 to 10 GPM, \$230.

FTB4807, 0.2 to 15 GPM, DPF701, panel meter, \$654 + 260 = \$914.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters