



Sanitary Turbine Flowmeters

FTB-970A Series Starts at
\$1166




- ✓ NIST Certificate Supplied Standard
- ✓ Sizes Available from ¼ to 3" Tri-Grip™
- ✓ Flow Rates from 0.5 to 650 GPM
- ✓ Suitable for Cleaning in Place (CIP)

FTB-970A Series sanitary turbine flowmeters are available in 11 sizes, from ¼ to 3" with standard Tri-Grip™ (Tri-Clamp® compatible) fittings. Covering flow rates from 0.5 to 650 GPM, these flowmeters are constructed of suitable materials for CIP.

Specifications

Accuracy and Linearity: ±0.5% rdg
Repeatability: ±0.1% rdg or better
Temperature Range:
 -73 to 232°C (-100 to 450°F)
 -268 to 65°C (-450 to 150°F)
 for FTB-971AT
Signal Output: 30 mV p-p minimum



FTB-973A, \$1166, shown actual size.

Use the FTB-970A Series turbine flowmeter with the DPF701 Series flow indicator, \$260. Visit omega.com/dpf701 for details.



Materials of Construction: 304 SS except as noted below
Rotor: 17-4 PH SS
Bearings: Tungsten carbide sleeve
Electrical: 2-wire connector (included)
Maximum Pressure Drop: 4 psid

Compatible Meters: DPF701, DPF402, DPF70 with FLSC-AMP, DPF10, FC20, 21, 22. Also FLSC-60 Series. Visit omegainstrument.info

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)								
Model No.	Price	Tri-Clamp Size (in)	Flowmeter Line Size (in)	Linear Flow Range (US GPM)	Length mm (in)	Approx. Weight kg (lb)	Nominal K Factor (pulses/gal)	Operating Pressure (psig)
FTB-971AB	\$1166	¾	¼	0.5 to 3.5	102 (4.0)	0.45 (1)	15,000	1500
FTB-972A	1166	¾	⅜	0.75 to 5.0	102 (4.0)	0.45 (1)	6000	1500
FTB-973A	1166	¾	½	1.25 to 9.5	102 (4.0)	0.45 (1)	3160	1500
FTB-974A	1166	¾	⅝	1.75 to 16	102 (4.0)	0.45 (1)	5300	1500
FTB-975A	1166	1½	¾	2.5 to 29	127 (5.0)	0.45 (1)	1035	600
FTB-976A	1172	1½	1	4 to 60	127 (5.0)	1.36 (3)	500	600
FTB-977A	1206	1½	1¼	6 to 93	127 (5.0)	1.36 (3)	320	600
FTB-978A	1325	1½	1½	8 to 130	127 (5.0)	2.27 (5)	230	600
FTB-979A	1469	2	2	15 to 225	152 (6.0)	2.27 (5)	133	450
FTB-980A	1705	2½	2½	25 to 400	191 (7.5)	2.73 (6)	75	400
FTB-981A	2197	3	3	40 to 650	241 (9.5)	3.18 (7)	46.1	350

Comes complete with operator's manual, mating electrical connector and NIST certificate.
 Units can also be ordered as systems with the FLSC-60 Series signal conditioners, visit omega.com/flsc60
Ordering Examples: FTB-976A, flowmeter with 1½" tri-clamp size, 4 to 60 GPM flow rate, \$1172.
 SYS/FTB-972A/FLSC-62A, sanitary turbine flowmeter for ¾" line (¾" Tri-Grip™ fitting) with 4 to 20 mA output signal conditioner, \$1166 + 431 = \$1597.

Recommended Reference Book: Chemical Process Equipment, FW-402, \$175. Visit omega.com/bobi for Additional Books



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters