

# HANDHELD DIGITAL AIRFLOW/ TEMPERATURE METERS

HHF92A  
**\$169**



Optional†



HHF92A, \$169, shown smaller than actual size with rugged carrying case (included).

- ✓ CFM Function
- ✓ Measures Air Velocity and Temperature
- ✓ Dual LCD Display
- ✓ Min/Max/Avg Air Velocity Measurements
- ✓ Auto Power Shut Off
- ✓ Battery Powered (9V Alkaline Included)

## SPECIFICATIONS

Air Flow	Resolution
80 to 6900 ft/min	1.00
0.4 to 35 m/sec	0.01
0.9 to 78 mph	0.10
0.8 to 68 knots	0.10
1.4 to 126 km/hr	0.10
<b>Accuracy:</b>	
80 to 6900 ft/min	±3% of full scale
0.4 to 35 m/sec	±3% of full scale

Temperature	Resolution	Accuracy
-10 to 50°C	0.1	±0.6°C
14 to 122°F	0.1	±1.0°F

**Battery:** 9V alkaline (included)

**Battery Life:**  
100 hr (under normal usage)

**Display:** LCD

**Display Size:** 37 x 42 mm (1½ x 1½")

**Max. Reading:** 9999

**Dimensions:**

183 x 76 x 45 mm (7.2 x 3 x 1.8")


**Fan Diameter:** 70 mm (2¾")

**Auto Power Off:** 20 minutes

**Data Hold:** Standard

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
HHF92A	\$169	Anemometer kit
CAL-3-FLOW†	225	NIST traceable 4-point calibration certificate
MN1603	3	Replacement 9V battery
CM-4339	135	Reference Book: Flow Measurement Methods and Applications 

OMEGA's HHF92A digital anemometer measures airflow in several different units: ft/min, mph, knots, meters/sec and km/h. Other features include the ability to measure temperature in °F or °C, and to give min/max/avg air velocity readings.

Comes complete with hard carrying case, integral probe, 9V battery and operator's manual.  
**Ordering Example:** HHF92A, handheld anemometer/thermometer, \$157.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters