



pH Benchtop Meter with RS232 Communications

PHB-550R
\$439



PHB-550R, \$439, shown smaller than actual size.

- ✓ Dual Display: pH and Temperature
- ✓ Automatic or Manual Temperature Compensation
- ✓ Store Up to 20 Readings for Later Recall
- ✓ Display Min/Max Readings
- ✓ Auto Shut-Off after 10 Minutes of Non-Use
- ✓ Digital Display with Backlight
- ✓ RS232 Communications

The PHB-550R is a microprocessor-based pH/mV/temp benchtop meter with splashproof housing. Via an RS232 interface, the user can upload data to a PC.

Specifications

Range/Resolution/Accuracy:

Measurement	Range	Resolution	Accuracy
pH	0 to 14	0.01	0.02
mV	±1999	1	2
Temp (°F)	32 to 212	0.1	0.5
Temp (°C)	0 to 100	0.1	0.3

pH Electrode: Glass, 0 to 14 pH, 0 to 80°C (32 to 176°F)

Temperature Probe: Stainless steel, 100 L x 6.4 mm D (3.9 x 0.25"), 0.8 m (34") cable

Compensation: ATC, 0 to 100°C (32 to 212°F) or MTC

Calibration: pH 1.68, 4, 7, 10, 12.45 (preset)

Power: 9 Vac adaptor

Dimensions: 190 H x 158 W x 70 mm D (7.5 x 6.2 x 2.7")

Weight: 585 g (1.3 lb)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
PHB-550R	\$439	pH/mV/temp benchtop meter
PHE-560	48	Replacement glass electrode
PHAT-500	54	Replacement temperature probe
PHE-1311	57	General purpose pH laboratory electrode
PHE-1411	70	Double junction pH laboratory electrode
PHE-2721	81	Double junction glass pH electrode
PHA-4	8	4.00 pH buffer solution 500 ml (1 pint) bottle
PHA-7	8	7.00 pH buffer solution 500 ml (1 pint) bottle
PHA-10	8	10.00 pH buffer solution 500 ml (1 pint) bottle

Comes complete with pH electrode, temperature probe, 2 buffer solutions (4 and 7 pH) and ac adaptor, software, communications cable and operator's manual.

Ordering Example: PHB-550R, pH benchtop meter, \$439.

Recommended Reference Book: 1001 Chemicals in Everyday Products, CM-4328, \$49.95 See Section Y for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters