

# Digital Conductivity/ Temperature/pH Tester Model PHH-10



Electronics  
Only



Integral Sample Cup  
Quick Field Determination

- ✓ Measures pH, Conductivity, and Temperature
- ✓ 3½ Digit LCD Display
- ✓ Rugged ABS Construction
- ✓ Automatic Battery Strength Compensation

Model PHH-10  
**\$549**

The PHH-10 tester measures temperature, pH, and conductivity in one versatile unit. Multiple range selection provides improved resolution for conductance measurement. The unit covers the full range of conductance and pH without the need for an adapter. Rugged ABS construction and integral sample cup make the PHH-10 the ideal choice for field applications and quick determinations. The conductivity probe and temperature sensor are incorporated into the sample cup. For easy replacement, the pH electrode is the only external connection.

### Specifications

**Range:** Conductance, 0 to 20, 0 to 200, 0 to 2000, 0 to 20,000 micromhos; Temperature, 0 to 160°F; pH, 0 to 14

**Accuracy:** Conductivity, ±2 % FS; Temperature, ±2°F; pH, ±0.01 pH at 25°C (77°F)

**Power:** 9 V battery (supplied), visual "LO BAT" warning

**Dimensions:** 203.4 x 88.9 x 50.8 mm (8 x 3 x 2")

**Weight:** 1.4 kg (3 lb)

**HIGHLIGHTED MODELS  
STOCKED FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
PHH-10-KIT	\$636	Conductivity/Temp/pH Tester with case, buffer solutions, pH electrode, and distilled water
PHH-10	549	Conductivity/Temp/pH Tester with case
PHE-1010	70	Replacement electrode
PHA-101	18	Buffer solution kit

### Conductivity Standardizing Solutions

Model No.	Price	Description
CDS-45	\$10/qt	45 µmhos/cm solution
CDS-450	10/qt	450 µmhos/cm solution
CDS-1500	10/qt	1500 µmhos/cm solution
CDS-4500	10/qt	4500 µmhos/cm solution

Ordering Example: PHH-10-KIT complete tester kit with CDS-45 45 µmho/cm standardizing solution, \$636 + 10 = \$646.



PHH-10-KIT includes case, buffer solutions, pH electrode, and distilled water, \$636.

**E** CONDUCTIVITY INSTRUMENTATION



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters