

OMEGAFLEX® LOW-DENSITY POLYETHYLENE TUBING



TYPE-1418-100
\$15
Basic 100'
Spool

Because of its tendency to develop stress cracks, polyethylene tubing should not be used with barbed fittings. Use compression-type fittings instead.

SPECIFICATIONS*

Specific Gravity: 0.921

Tensile Strength, psi: 1600

Hardness, Shore D: 50

Elongation at Break, %: 500

Brittle Temperature: -60°C (-76°F)

Maximum Operating Temperature: 60°C (140°F)

* Specifications shown are typical and are meant only as a guide. Field testing is recommended to find actual values in the given application.

Note: The listed working pressures are based on a short-term burst using a 4 to 1 safety factor.



Specialty Tubing Available!



To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

¼ to 1¾" OD TUBING

Model No.	Price	Standard Length (ft)	Wall (in)	OD (in)	ID (in)	Working psi at 73°F	Weight (lb)
TYPE-14170-500**	\$50	500	0.04	¼	0.17	135	5.25
TYPE-1418-500*	85	500	⅛	¼	⅛	180	7.35
TYPE-1418-100	15	100	⅛	¼	⅛	180	1.47
TYPE-516316-500	125	500	⅛	⅝	⅜	140	10
TYPE-516316-100	25	100	⅛	⅝	⅜	140	1.96
TYPE-3814-100**	30	100	⅛	¾	½	120	2.45
TYPE-1238-100	40	100	⅛	½	⅜	90	3.4
TYPE-1238-500*	200	500	⅛	½	⅜	90	17.15
TYPE-5812-100*	45	100	⅛	¾	½	70	4.4
TYPE-3458-100	45	100	⅛	¾	⅝	60	5.4
TYPE-7858-100	85	100	⅛	¾	⅝	100	11.18
TYPE-134-100	95	100	⅛	1	¾	90	13.7
TYPE-178-100	70	100	⅛	1	⅝	45	7.4
TYPE-1141-100	130	100	⅛	1¼	1	72	17.6
TYPE-112114-50	140	50	⅛	1½	1¼	59	10.8
TYPE-134112-50	195	50	⅛	1¾	1½	50	12.8

Standard color is natural (clear).

Color Options: Add the following suffix, no additional charge: * -BK = black.

** -RE = red, -YE = yellow, -GR = green, -BL = blue and -BK = black.

Ordering Example: TYPE-3814-100-BL 100', ¾" OD and ½" ID low-density blue polyethylene tubing with working psi of 120, \$30.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters