


OMEGAFLEX® Chemical Tubing PFA FORMULATION

TYTP Series
Starts at
\$35
25' Spool



PFA tubing is a flexible tubing with an almost transparent appearance. Unlike pipe, PFA tubing can be extruded in very long, continuous lengths, thus allowing for fewer connections.

PFA tubing from OMEGA® is manufactured from the highest-grade resins, which provide outstanding physical and chemical-stress crack resistance and superior flex-life. Like pipe, PFA tubing has excellent chemical resistance properties and can be used in temperatures ranging from -196 to 260°C (-320 to 500°F).

SPECIFICATIONS*

Hardness, Shore D: 60
Specific Gravity: 2.15
Elongation at Break: 300%
Brittle Temperature: 170°C (-275°F)
Service Temp: -196 to 260°C (-320 to 500°F)
ASTM: 3307

Accessory

Model No.	Price	Description
FW-304	\$100	Reference Book: Piping Calculations Manual

*Specifications given are typical. Field testing is recommended to find the actual operating specifications in the given application.

Notes: PFA is clear in color and can be heat sealed and heat bonded.

Sold in standard coil lengths of 25, 50, and 100'. PFA packages have no splices.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

1/8" to 3/8" OD TUBING

Model No.	Price	Std Length (ft)	Wall (in)	OD (in)	ID (in)	psi @ 73°F
TYTP-116132-100	\$125	100	0.016	1/8	1/16	345
TYTP-18116-25	35	25	0.03	1/8	1/16	325
TYTP-18116-50	70	50	0.03	1/8	1/16	325
TYTP-18116-100	140	100	0.03	1/8	1/16	325
TYTP-316116-50	150	50	0.063	3/16	1/16	450
TYTP-316116-100	300	100	0.063	3/16	1/16	450
TYTP-532332-50	90	50	0.03	5/32	3/32	260
TYTP-532332-100	180	100	0.03	5/32	3/32	260
TYTP-31618-50	110	50	0.03	3/16	1/8	215
TYTP-31618-100	220	100	0.03	3/16	1/8	215
TYTP-1418-25	90	25	0.063	1/4	1/8	340
TYTP-1418-50	180	50	0.063	1/4	1/8	340
TYTP-1418-100	360	100	0.063	1/4	1/8	340
TYTP-14532-25	100	25	0.047	1/4	5/32	255
TYTP-14532-50	200	50	0.047	1/4	5/32	255
TYTP-14532-100	400	100	0.047	1/4	5/32	255
TYTP-14316-50	160	50	0.03	1/4	3/16	160
TYTP-14316-100	320	100	0.03	1/4	3/16	160
TYTP-516316-25	150	25	0.063	5/16	3/16	275
TYTP-516316-50	300	50	0.063	5/16	3/16	275
TYTP-516316-100	600	100	0.063	5/16	3/16	275
TYTP-51614-25	100	25	0.03	5/16	1/4	130
TYTP-51614-50	200	50	0.03	5/16	1/4	130
TYTP-51614-100	400	100	0.03	5/16	1/4	130
TYTP-3814-25	150	25	0.063	3/8	1/4	225
TYTP-3814-50	300	50	0.063	3/8	1/4	225
TYTP-3814-100	600	100	0.063	3/8	1/4	225

Ordering Example: TYTP-532332-50, 50' of tubing, 0.03" wall, 5/32" OD, 3/32" ID, \$90.


T-X

OMEGAFLEX® Chemical Tubing PFA FORMULATION

■ MOST POPULAR MODELS HIGHLIGHTED!

Specialty Tubing Available!

To Order (Specify Model Number)						
4 to 16 mm OD Metric Diameters						
Model No.	Price	Std Length (ft)	Wall (mm)	OD (mm)	ID (mm)	psi @73°F
TYTP-42-50	\$110	50	1	4	2	400
TYTP-42-100	220	100	1	4	2	400
TYTP-64-25	65	25	1	6	4	265
TYTP-64-50	130	50	1	6	4	265
TYTP-64-100	260	100	1	6	4	265
TYTP-86-25	100	25	1	8	6	200
TYTP-86-50	200	50	1	8	6	200
TYTP-86-100	400	100	1	8	6	200
TYTP-108-25	140	25	1	10	8	160
TYTP-108-50	280	50	1	10	8	160
TYTP-108-100	560	100	1	10	8	160
TYTP-1210-25	160	25	1	12	10	130
TYTP-1210-50	320	50	1	12	10	130
TYTP-1210-100	640	100	1	12	10	130



Sold in standard lengths of 25, 50, and 100'.

Ordering Example: TYTP-86-50, 50' of tubing, 1 mm wall, 8 mm OD, 6 mm ID, \$200.

3/8 to 2 1/2" OD TUBING						
Model No.	Price	Length (ft)	Wall (in)	OD (in)	ID (in)	psi @ 73°F
TYTP-38516-25	\$120	25	0.03	3/8	5/16	105
TYTP-38516-50	240	50	0.03	3/8	5/16	105
TYTP-38516-100	480	100	0.03	3/8	5/16	105
TYTP-716516-25	200	25	0.063	7/16	5/16	195
TYTP-716516-50	400	50	0.063	7/16	5/16	195
TYTP-716516-100	800	100	0.063	7/16	5/16	195
TYTP-71638-25	140	25	0.03	7/16	3/8	90
TYTP-71638-50	280	50	0.03	7/16	3/8	90
TYTP-71638-100	560	100	0.03	7/16	3/8	90
TYTP-1238-25	200	25	0.063	1/2	3/8	425
TYTP-1238-50	400	50	0.063	1/2	3/8	425
TYTP-1238-100	800	100	0.063	1/2	3/8	425
TYTP-12716-25	150	25	0.03	1/2	7/16	80
TYTP-12716-50	300	50	0.03	1/2	7/16	80
TYTP-12716-100	600	100	0.03	1/2	7/16	80
TYTP-916716-25	420	25	0.063	9/16	7/16	150
TYTP-916716-50	840	50	0.063	9/16	7/16	150
TYTP-916716-100	1680	100	0.063	9/16	7/16	150
TYTP-91612-25	225	25	0.03	9/16	1/2	70
TYTP-91612-50	450	50	0.03	9/16	1/2	70
TYTP-91612-100	900	100	0.03	9/16	1/2	70
TYTP-5812-25	280	25	0.063	5/8	1/2	135
TYTP-5812-50	560	50	0.063	5/8	1/2	135
TYTP-5812-100	1120	100	0.063	5/8	1/2	135
TYTP-3458-25	275	25	0.063	3/4	5/8	115
TYTP-3458-50	550	50	0.063	3/4	5/8	115
TYTP-3458-100	1100	100	0.063	3/4	5/8	115
TYTP-08334-25	280	25	0.04	0.83	3/4	65
TYTP-178-25	460	25	0.063	1	7/8	85
TYTP-1101-5	150	5 Straight	0.05	1.10	1	60
TYTP-1181-5	150	5 Straight	0.063	1 1/8	1	75

Ordering Example: TYTP-5812-100, 100', 0.063" wall, 5/8" OD, 1/2" ID, \$1120.

T-X



Accessory

Model No.	Price	Description
FW-321	\$80	Reference Book: Introduction to Practical Fluid Flow



T



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters