

# WRAP-AROUND TOTE TANK HEATERS

TOTE Series Starts at

**\$1469**



- ✔ Fits Any Tote Tank from 1 to 1.2 m (40 to 48") Square
- ✔ Comes in Heights of 0.9, 1.1 or 1.2 m (36, 42 or 48")
- ✔ 2 Heating Zones
- ✔ 2 Built-In Adjustable Thermostats
- ✔ 2 Built-In High-Limit Thermostats
- ✔ Adjustable Nylon Straps with Buckles
- ✔ Flexible Silicone-Impregnated Cloth Facing and Liner
- ✔ 6 mm (¼") Fiberglass Insulation
- ✔ 1.8 m (6') Power Cord

The OMEGA® TOTE Series tote tank heaters are flexible wrap-around surface heaters offered in different sizes based on height. These heaters provide a quick, easy, non-invasive way to warm your product. They fit nearly every standard tote tank utilizing adjustable nylon straps with buckles. There are 3 straps for placing around the tank and 2 for across the top. Units include an adjustable thermostat and a manual reset high-limit thermostat for each of the 2 zones.

**SPECIFICATIONS**

**Adjustable Thermostat Setting:** 10 to 70°C (50 to 160°F)

**High-Limit Thermostat Setting:** Approximately 90°C (195°F)

**High-Limit Thermostat Reset:** Manual



TOTE481-ADJ/120V, \$1694, shown smaller than actual size.

**Maximum Exposure Temperature:** 230°C (450°F)

**Outer Sheath and Liner:** Silicone impregnated

**Attachment Method:** Nylon straps with adjustable buckles

**Fiberglass Insulation:** 6 mm (0.25")

**Total Blanket Length:** Approximately 5 m (16.5')

**Heated Length:** Approx 4.1 m (13.5')

**Height:** 915 mm (36"), 1065 mm (42") or 1220 mm (48")

**Wattage:** 1440 or 2880 W

**Power Cord:** 1.8 m (6') with standard power plug

**Power:** 120 or 240 Vac

**MOST POPULAR MODELS HIGHLIGHTED!**

**To Order (Specify Model Number)**

Model No.	Price	Description	Weight
TOTE361-ADJ/120V	\$1469	Tote heater with thermostat, 120V, 1440 W, 0.9 m (36") height	18 kg (40 lb)
TOTE362-ADJ/240V	1469	Tote heater with thermostat, 240V, 2880 W, 0.9 m (36") height	18 kg (40 lb)
TOTE421-ADJ/120V	1659	Tote heater with thermostat, 120V, 1440 W, 1.1 m (42") height	20 kg (45 lb)
TOTE422-ADJ/240V	1659	Tote heater with thermostat, 240V, 2880 W, 1.1 m (42") height	20 kg (45 lb)
TOTE481-ADJ/120V	1694	Tote heater with thermostat, 120V, 1440 W, 1.2 m (48") height	22 kg (50 lb)
TOTE482-ADJ/240V	1694	Tote heater with thermostat, 240V, 2880 W, 1.2 m (48") height	22 kg (50 lb)
TOTE-COVER	441	Tote insulated top cover	

*Comes complete with adjustable and high-limit thermostats for each of 2 heat zones.*

**Ordering Examples:** TOTE361-ADJ/120V, tote heater with thermostat, 120V, 1440 W, 0.9 m (36") height, and TOTE-COVER, tote insulated top cover, \$1469 + 441 = **\$1910**. TOTE421-ADJ/120V, tote heater with thermostat, **\$1659**.

Recommended Reference Book: Applied Process Design, PE-1038, \$175. Visit [omega.com/bobi](http://omega.com/bobi) for Additional Books



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters