

# FREQUENCY CALIBRATOR

## RUGGED, EASY-TO-USE

CL250  
\$595



For Pressure Applications, See PCL240 on Page A-26.

- ✓ High Accuracy
- ✓ Source and Read Capability
- ✓ Rugged, Dust-Tight, Water-Resistant Case
- ✓ Easy-to-Read Super-Twist LCD
- ✓ Intuitive Controls Make Operation Easy
- ✓ 9V Battery (Included)

Because it can generate or read frequencies from 1 count per minute to 100 kHz, the OMEGA® CL250 frequency calibrator can be used for a wide range of flow measuring applications. This rugged instrument combines laboratory-grade accuracy with easy-to-use pushbutton controls. Step and ramp keys allow both large and small output changes.

### SPECIFICATIONS

**Ranges:** 0 to 100 kHz, 0 to 1000 Hz, 0 to 100 cpm

**Accuracy:** ±0.01% FS, ±1 LSD @ 18 to 28°C (64 to 82°F)

**Max Driving Load:** 5 mA (1 kΩ load min)

**Operating Temp:** 0 to 50°C (32 to 122°F)

**Storage Temp:** -20 to 60°C (-4 to 140°F)

**Temperature Stability:** 0.005% FS/°C @ 28 to 50°C (82 to 122°F)

**Output Signal:** 5V p-p square wave

**Input Signal:** 1 to 100V p-p

**Step Size:** 10% of range

**Scroll Size:** 0.1% of range

**Weight:** 340 g (12 oz)

**Dimensions:** 36 D x 80 W x 145 mm H (1.43 x 3.15 x 5.7")



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.



CL250, case included, front and back shown.

CL250, \$595, shown actual size.

INSTRUMENTATION D

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
CL250	\$595	Frequency calibrator

Comes complete with test leads, carrying case, 9V battery, NIST calibration certificate and operator's manual.

**Ordering Example:** CL250, frequency calibrator, \$595.

OCW-1 OMEGACARE<sup>SM</sup> extends standard 1-year warranty to a total of 2 years (\$59), \$595 + 59 = \$654.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters