

# DIN STYLE CONNECTORS FOR TRANSDUCERS

CX5300 Series  
Starts at  
**\$10**

ISO 4400 standards. They are used as protective electrical enclosures for electrical connections, primarily on pressure transducers and solenoid valves.



CX5300, \$10, shown smaller than actual size.

**MOST POPULAR MODELS HIGHLIGHTED!**

- ✓ Use Where Service and Rapid Installation are Necessary
- ✓ Made According to DIN 43650/ISO 4400 Standards
- ✓ Strain-Relief Gland or Conduit-Fitting Design

To Order (Specify Model Number)		
MODEL NO.	PRICE	SIZE/DESCRIPTION
CX5300	\$10	20 mm/3 contacts plus ground terminal with PG9 gland
CX5301	10	20 mm/3 contacts plus ground terminal with 12.7 mm (1/2") conduit fitting
CX5302	15	9 mm/3 contacts plus ground terminal with PG7 gland
CX5303	25	9 mm/3 contacts plus ground terminal with 12.7 mm (1/2") conduit fitting (not shown)

The CX5300 Series connectors are made according to DIN 43650/

**Ordering Example:** CX5300, 20 mm sub-micro DIN style connector with 3 contacts plus ground terminal and PG9 cable gland, \$10.

## TRANSDUCER CONNECTORS

- ✓ Heavy-Duty Construction
- ✓ Rated to 105°C (215°F)
- ✓ Solderless Connection
- ✓ 22-26 AWG Wire Size
- ✓ Flame-Retardant Thermoplastic Shells
- ✓ High-Conductivity, Gold-Plated over Nickel-Plated Contacts



CX136-4, \$2.50, shown actual size.

CX136 Series  
All Models  
**\$2.50**

**MOST POPULAR MODEL HIGHLIGHTED!**

To Order (Specify Model Number)				
MODEL NO.	PRICE	NO. OF CONTACTS	COMPATIBLE SENSORS	SENSOR PAGE NO.
CX136-3	\$2.50	5	PX141/142/143	B-72
			PX162/163/164	B-73
			PX170/PX26	B-16-17
CX136-4	2.50	4	PX137	B-20
			PX138/139	B-74-75

**Ordering Example:** CX136-4, connector for PX26 transducer, \$2.50.

CX136-4, connector, \$2.50 shown actual size.

CX106-4 contact pins.

## OEM STYLE CONNECTORS

CX106-4  
**\$1**

- ✓ High-Conductivity, Tin-Plated Over Brass Contacts
- ✓ Contacts Included

- ✓ Durable Valox® Shell
- ✓ Rated to 125°C (257°F)
- ✓ Solder/Crimp Contacts
- ✓ 16-20 AWG Wire Size



PX106-CONNECTOR, \$6, (connector only) shown actual size.

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
MODEL NO.	PRICE	DESCRIPTION
PX106-CONNECTOR	\$6	Spare connector body for PX106 (contact pins sold separately)
CX106-4	1	3-contact pins for PX106-CONNECTOR

**Ordering Examples:** PX106-CONNECTOR, connector only for PX106 transducer, \$6. CX106-4, contact pins, package of 3, \$1.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters