

# MECHANICAL FORCE GAGES

## INDUSTRIAL AND LABORATORY GRADE MODELS

### DFG80 Series

Starts at  
**\$560**

- ✓ ±0.3% and 0.1% Accuracy Models
- ✓ Rugged Die-Cast Aluminum Housing
- ✓ Tare Ring and Peak Hold
- ✓ Ergonomic Design, Economical Price
- ✓ Mountable to Test Fixtures



DFG82 is sold as a complete kit including a hard case, measuring adaptors (flat head, cone, chisel, notched, small hook, large hook, and fork), and extension rod.

#### SPECIFICATIONS

Accuracy:  
DFG81: 0.3%  
DFG82: 0.1%

Dimensions:  
200 H x 67 W x 46 mm D  
(7.87 x 2.64 x 1.81")

DFG81-100, \$560, shown actual size.

For Complete Details Visit  
[omega.com/xxx](http://omega.com/xxx)

The ruggedly constructed DFG80 gages will withstand harsh industrial environments yet remain accurate to ±0.3%. These gages are sold as kits complete with gage, hard carrying case, measuring tips, and extension rod. The ergonomic design makes the DFG80 ideal for handheld use. They can also be mounted on a test fixture.

**MOST POPULAR MODELS HIGHLIGHTED!**

#### To Order (Specify Model Number)

0.3% ACCURACY MODEL NO.	0.1% ACCURACY MODEL NO.	lb	0.3% ACCURACY MODEL NO.	0.1% ACCURACY MODEL NO.	kg	0.3% ACCURACY MODEL NO.	0.1% ACCURACY MODEL NO.	N	0.3% DFG81 PRICE	0.1% DFG82 PRICE
DFG81-2	DFG82-2	2	DFG81-1KG	DFG82-1KG	1	DFG81-10N	DFG82-10N	10	\$560	\$600
DFG81-5	DFG82-5	5	DFG81-2KG	DFG82-2KG	2	DFG81-20N	DFG82-20N	20	560	600
DFG81-10	DFG82-10	10	DFG81-3KG	DFG82-3KG	3	DFG81-30N	DFG82-30N	30	560	600
DFG81-20	DFG82-20	20	DFG81-5KG	DFG82-5KG	5	DFG81-50N	DFG82-50N	50	560	600
—	—	—	DFG81-10KG	DFG82-10KG	10	DFG81-100N	DFG82-100N	100	560	600
DFG81-30	DFG82-30	30	DFG81-20KG	DFG82-20KG	20	DFG81-200N	DFG82-200N	200	560	600
DFG81-50	DFG82-50	50	DFG81-30KG	DFG82-30KG	30	DFG81-300N	DFG82-300N	300	560	600
DFG81-100	DFG82-100	100	DFG81-50KG	DFG82-50KG	50	DFG81-500N	DFG82-500N	500	560	600

Comes complete with gage, hard carrying case, measuring tips, and extension rod.

Ordering Example: DFG81-10KG, complete kit with 10 kg range digital force gage, \$560.

DFG82-10, complete kit with 10 lb range digital force gage, \$600.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters