

10-CHANNEL PORTABLE STRAIN GAGE MONITORING SYSTEM



DMD-22
\$4730

DMD-22, \$4730, shown smaller than actual size.



- ✓ Reads Directly in Microstrain and Engineering Units
- ✓ Independent Zeroing on Each Channel
- ✓ High Accuracy and Resolution

The DMD-22 is a portable, 10-channel strain gage system that combines the powerful features of the DMD-21 and DMD-21SB. Independent zeroing on each channel eliminates subtracting unstrained readings to arrive at true strained results. Pushbutton front keys and clearly labeled switches ensure accurate strain gage measurements.

Selectable bridge configuration via internal fixed resistors eliminates complex and time-consuming external bridge completion. Readings in microstrain take the mystery out of transposing millivolt readings to strain readings.

SPECIFICATIONS

Linearity: 0.02% FS
Range: $\pm 19.999 \mu\epsilon$
Zero Balance: 50% FS
Resolution: $1 \mu\epsilon$
Excitation: 2, 5 or 10 Vdc
Bridge Type: $\frac{1}{4}$, 120 and 350 Ω ; $\frac{1}{2}$ and full, $>120 \Omega$ (internal bridge completion resistors)

Gage Factor: 1 to 2.99
Operating Temp: 5 to 35°C (41 to 95°F)
Thermal Effects: Zero, $0.5 \mu\epsilon/^\circ\text{C}$ ($0.3 \mu\epsilon/^\circ\text{F}$) span, 0.0005% rdg/ $^\circ\text{C}$ (0.003% rdg/ $^\circ\text{F}$)
Analog Output: ± 2 Vdc (over $\pm 20,000 \mu\epsilon$, DC to 20 kHz)
Input Impedance: 1000 M Ω
Power: 115 or 230 Vac @ 50/60 Hz; lead-acid rechargeable batteries (included), 8 hours
Dimensions: 419 W x 152 H x 356 mm D (16.5 x 6 x 14")
Connections: Rear screw terminals
Weight: 7 kg (15.5 lb)

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
DMD-22	\$4730	Portable 10-channel strain gage monitor

Comes with operator's manual.

Ordering Example: DMD-22, portable, 10-channel strain gage monitor, \$4730.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters