

HIGH-ACCURACY DIGITAL BAROMETER KIT

WITH NIST-TRACEABLE CERTIFICATION

DPI740-KIT
\$2415



Standard

- ✓ NIST-Traceable Calibration Certificate Included
- ✓ Very High Accuracy: $\pm 0.02\%$ FS
- ✓ Measures Absolute or Sea Level Barometric Pressure
- ✓ Altitude Mode with Local Height and Temperature Corrections
- ✓ Stability Better Than 100 ppm per Year
- ✓ Standard RS232 Communications



Kit comes complete with rugged transit case, soft carrying case, RS232 cable, and 3 "AA" batteries.



DPI740-KIT, \$2415, shown smaller than actual size.

OMEGA's DPI740 is a high-accuracy, handheld barometer suitable for the most demanding field or laboratory applications. It can measure absolute barometric pressure or barometric pressure corrected to sea level. Pressure can be displayed in 1 of 24 different engineering units. In addition, the DPI740 can display altitude in feet or meters.

SPECIFICATIONS

Measuring Range:

23 to 34 inHg absolute

Accuracy: $\pm 0.02\%$ FS @

-10 to 50°C (14 to 122°F)

Operating Temp: -10 to 50°C

(14 to 122°F)

Storage Temp: -40 to 71°C

(-40 to 160°F)

Safe Overpressure: 0 to 118 inHg will not cause calibration change

Resolution: 0.0003 inHg

Display Update: 2 readings per second

Operating Modes: Local pressure, sea level pressure from user-set height, altitude from user-set datum

Units of Measure:

24 selectable scales for pressure, feet or meters for altitude

Process Features: Max/min, reading store, tare and programmable filter available in all modes

Pressure Media: Non-corrosive gases only

Pressure Fitting: Hose fitting for 4 mm ID, 6 mm OD (0.157 x 0.236") flexible tubing

Sealing Standard: NEMA 12 (IP54)

Power: 3 "AA" batteries (included) provides 20 hours of continuous operation

Dimensions: 190 H x 89 W x 36 mm D (7.5 x 3.5 x 1.4")

Weight: 0.5 kg (1.1 lb)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
DPI740-KIT	\$2415	Handheld barometer kit

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
DPI740-BATT	\$70	1 Ni-Cad battery (optional, 3 required)
DPI740-CHARGER	95	115/220 Vac battery charger (optional)

Comes complete with rugged transit case, soft carrying case, RS232 cable, 3 "AA" batteries, NIST calibration certificate and operator's manual.

Ordering Example: DPI740-KIT, handheld barometer kit, 3 of DPI740-BATT, adds rechargeable batteries and DPI740-CHARGER, charger to kit, \$2415 + (3 x 70) + 95 = \$2720.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters