

LOW-PRESSURE MANOMETER

WITH 1.999 inH₂O LOW RANGE

10.04 inH₂O HIGH RANGE

HHP-103
\$579



- ✓ High Resolution to 0.001 inH₂O
- ✓ Measure Differential Gage or Vacuum
- ✓ Auto-Ranging Display
- ✓ One-Handed Operation
- ✓ Rugged, Water-Resistant Case

The HHP-103 handheld manometer is designed for one-handed industrial or laboratory use. The custom-molded case allows heavy use in humid environments. A high-contrast LCD with backlight enables easy reading.

The HHP-103 can measure gage, vacuum, or differential pressures by venting the low and high ports to atmosphere. For greater precision, it offers both a low and high range.

See Section Y for a Selection of Scientific, Technical, and Reference Books Available from omega.com

HHP-103, \$579, shown actual size.



SPECIFICATIONS

Accuracy: 0.2% FS of high range

Operating Temperature: -10 to 50°C (14 to 122°F)

Compatible Media: Dry, non-corrosive gases

Power: 9V battery included (approx. 300-hr operation)

Zero Adjustment: Front-panel button

Display: 3½ digit, 13 mm (0.5"), backlight

Pressure Port: Tube fitting for 0.155" < ID > 0.195", OD < 0.24" Tygon® or silicon tubing (tubing not included)

Dimensions: 140 H x 70 W x 26 mm D (5.50 x 2.75 x 1.00")

Weight: 250 g (8.8 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	RANGE	
		LOW	HIGH
AUTO-RANGING, PUSHBUTTON-SELECTABLE ENGINEERING UNITS			
HHP-103	\$579	0 to 1.999 inH ₂ O	0 to 10.04 inH ₂ O

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
OS200-COVER	\$41	Protective rubber boot
TYTY-732532-50	40	15.2 m (50') Tygon tubing; 7/32" OD, 5/32" ID

Comes complete with 9V battery and operator's manual.

Ordering Example: HHP-103, auto-ranging air pressure meter with pushbutton-selectable engineering units and 0 to 1.999 inH₂O low-range and 0 to 10.04 inH₂O high range, OS200-COVER, protective rubber boot, and TYTY-732532-50, 15.2 m (50') of Tygon tubing, \$579 + 41 + 40 = \$660. Visit omega.com/tubing for additional tubing options.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters