

# ECONOMICAL DIGITAL HANDHELD MANOMETER 0 to 20 inH<sub>2</sub>O RANGE

HHP680  
**\$145**



- ✓ Max and Reading Hold
- ✓ Portable and Easy-to-Use
- ✓ Auto-Zero Power
- ✓ Switchable High Resolution:  
0.01/0.1" Water Column
- ✓ Comes with Tubing [60 cm (24")]  
and 1/8 NPT Fitting
- ✓ 4 "AAA" Alkaline  
Batteries Included
- ✓ Soft Carrying Case

The HHP680 is a low-cost, versatile handheld manometer. It comes with tubing, fitting, soft carrying case, and batteries. Typical applications include commercial and automotive HVAC.

## SPECIFICATIONS

**Display:** 3½ digit LCD with a maximum reading of 1999

**Range:** 0 to 20 inH<sub>2</sub>O

**Resolution:** 0.01/0.1"

**Low-Battery Indicator:**

The "HHP" displays

**Storage Temperature:**

-20 to 60°C (-4 to 140°F)

**Operating Temperature:**

0 to 40°C (32 to 104°F)

**Operating Relative Humidity:**

15 to 90% RH, non-condensing

**Accuracy:** ±2% at 23°C (73°F)

[±5°C (9°F), <75% RH]

**Dimensions:** 190 H x 44 W x 40 mm D

(7.5 x 1.7 x 1.6")

**Weight:** Approx. 150 g (5.3 oz)  
with batteries

**Batteries:** 4 "AAA" (included)

**Sensor:** Solid state

**Battery Life:** 150 hrs, typical usage; no measurable current when in off position

**Compatible Media:** Dry,  
non-corrosive gases



**VERSATILE!**

See Section Y for a  
Selection of Scientific,  
Technical, and Reference  
Books Available from  
[omega.com](http://omega.com)

60 cm (24") of  
tubing and 1/8 NPT  
adaptor included.

HHP680, \$145,  
shown actual size.

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
HHP680	\$145	Portable manometer with 0 to 20 inH <sub>2</sub> O range

Comes complete with 60 cm (24") of tubing, fitting, 4 "AAA" alkaline batteries, soft carrying case and operator's manual.

**Ordering Example:** HHP680, handheld manometer, \$145.

A

PRESSURE INSTRUMENTS



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters