



Precision Handheld Pumps For Pressure and Vacuum Calibration

HPP Series
Starts at
\$389



For Complete
Details Visit
[omega.com/
hpp_series](http://omega.com/hpp_series)

- ✓ Pneumatic Models for Vacuum and Pressure to 41 bar (600 psi)
- ✓ Hydraulic Model for 0 to 690 bar (0 to 10,000 psi)
- ✓ Precision Vernier for Fine Adjustments
- ✓ Designed for High Reliability and High Performance

OMEGA's HPP Series precision calibration pumps are designed to provide long term reliability in harsh environments. Four models are available to cover ranges from vacuum up to 690 bar (10,000 psi). Pumps can be purchased separately or as a kit that includes a carrying case, tubing and fittings.

The HPP-100 and HPP-VAC are economical pumps designed for 0 to 6.9 bar (0 to 100 psi) or 0 to -0.95 bar (0 to -28 inHg vacuum). Both models feature dual O-rings on all pistons for smooth operation with zero leakage. A "mash proof" schrader valve replaces the needle valve commonly used for the vent.



HPP-VAC
pneumatic
pump, \$389.



HPP-600 pneumatic
pump, \$589.

HPP-600 The HPP-600 is a pneumatic pump that can generate both vacuum and pressure. It covers a range from -0.95 bar (28 inHg) vacuum to 41 bar (600 psi) pressure. Dual O-rings, oversized check valves, and a "mash proof" vent valve ensure smooth, trouble free operation.

HPP-10K The HPP-10K hydraulic pump can generate pressure from 0 to 690 bar (0 to 10,000 psi). It is compatible with most hydraulic fluids, oils and water. A precision stroke control adjustment allows for fast priming or shorter stroke for easier pumping at high pressure. It features a shatter proof reservoir, triple filtration system and a built-in pressure relief valve.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Pumps Only

Model No.	Price	Description
HPP-100	\$389	Handheld pneumatic pressure pump, 0 to 6.9 bar (0 to 100 psi)
HPP-VAC	389	Handheld pneumatic vacuum pump, 0 to -0.95 bar (0 to -28 inHg vacuum)
HPP-600	589	Handheld pneumatic vacuum/pressure pump, -0.95 to 41 bar (-28 inHg to 600 psi)
HPP-10K	889	Handheld hydraulic pressure pump, 0 to 690 bar (0 to 10,000 psi)

Pump Kits (Kits Include Pump, Carrying Case, Tubing with Fittings)

HPP-100-KIT	\$485	HPP-100 pump, carrying case, HPP-HOSE and 64 mm (2 1/2") gauge
HPP-VAC-KIT	485	HPP-VAC pump, carrying case, HPP-HOSE and 64 mm (2 1/2") gauge
HPP-600-KIT	697	HPP-600 pump, carrying case and HPP-600-HOSE
HPP-10K-KIT	999	HPP-10K pump, carrying case, fluid bottle and HPP-10K-HOSE

Accessories

Model No.	Price	Description
HPP-HOSE	\$49	0.6 m (2') tubing with 1/8 NPT fittings for HPP-100 or HPP-VAC
HPP-600-HOSE	69	0.6 m (2') tubing with 1/8 NPT fittings for HPP-600
HPP-10K-HOSE	189	0.9 m (3') high pressure tubing for HPP-10K with (2) 1/4 BSPM self sealing test point adaptors
HPP-10K-FW	25	Replacement filters and washers for HPP-10K

Comes complete with operator's manual. Units with BSP fittings also include NPT adaptors.

Ordering Examples: HPP-100, handheld pressure pump, 0 to 6.9 bar (0 to 100 psi), \$389.

HPP-600-KIT, vacuum to 41 bar (600 psi) pump kit with carrying case, tubing and fittings, \$697.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters