

ALL STAINLESS STEEL TRANSDUCER MULTIMEDIA COMPATIBILITY HIGH-PERFORMANCE SILICON TECHNOLOGY

Engineered from
1 to 10,000 psi.

PX309 Series
Gage/Absolute Pressure
0 to 5 Vdc Output
0-1 to 0-10,000 psia
0-70 mbar to 0-690 bar

Starts at
\$225



- ✓ 1, 2, and 5 psi Low Pressure Ranges
- ✓ Rugged, Solid State Design
- ✓ All Stainless Steel
- ✓ High Stability, Low Drift
- ✓ 0.25% Accuracy
- ✓ RoHS Compliant
- ✓ IP65 Protection Class

SPECIFICATIONS

Excitation: 9 to 30 Vdc (<10 mA)
(reverse polarity and overvoltage protected)

Output: 0 to 5 Vdc

Accuracy: $\pm 0.25\%$ FS BSL at 25°C;
includes linearity, hysteresis and repeatability

Zero Offset: $\pm 2\%$ FSO;
 $\pm 4\%$ for 1 and 2 psi ranges

Span Setting: $\pm 2\%$ FSO;
 $\pm 4\%$ for 1 and 2 psi ranges

Total Error Band: $\pm 2\%$ FSO, includes linearity, hysteresis, repeatability, thermal hysteresis and thermal errors (except 1 psi = $\pm 4.5\%$ and 2 psi = $\pm 3\%$)

Long-Term Stability (1 Year):
 $\pm 0.25\%$ typical

Typical Life: 10 million cycles

Operating Temperature: -40 to 85°C
(-40 to 185°F)

Compensated Temperature:
>5 psi Range: -20 to 85°C (-4 to 185°F)
≤5 psi Range: 0 to 50°C (32 to 122°F)


Proof Pressure:
psia and ≤50 psig: 3x capacity or 20 psi, whichever is greater
≥100 psi: 2x capacity

PX309-100G5V, \$225,
shown actual size.



Cable style.

PX329-100G5V, \$275,
shown actual size.




Twist-lock style.

**Fast
Delivery!**

Metric thread
adaptors available,
see section C.

PX319-100G5V, \$225,
shown actual size.



mini DIN style
(connector
included).

Burst Pressure: 5x capacity or 25 psi,
whichever is greater

Response Time: <1 ms

Shock: 50 g, 11 ms half-sine shock

Vibration: ± 20 g

Wetted Parts: 316 SS for all psia
ranges and 1 to 50 psig; 17-4 PH SS for
ranges 100 to 10,000 psig

Pressure Port: 1/4-18 MNPT

Electrical Connections:

PX309: 1.5 m (5') 3-conductor cable

PX319: mini DIN connector with
mating connector included

PX329: Twist-lock connector,
mating connector sold separately
(PT06V-10-6S)

Weight: 155 g (5.4 oz) max

Note: Units 100 psig and above may be
subjected to vacuum on the pressure
port without damage

For alternative performance
specifications contact Engineering.

Order a
snubber to
protect your
pressure
transducer!




PS-4G, \$12.75, shown actual size.

Snubbers protect sensors
from fluid hammers/spikes.

VOLTAGE OUTPUT
PRESSURE TRANSDUCERS

B

RUGGED, GENERAL PURPOSE TRANSDUCER



LOW-PRESSURE RANGES HIGHLIGHTED

To Order (Specify Model Number)

RANGE		1.5 m CABLE CONNECTION	PRICE	MINI DIN CONNECTION	PRICE	TWIST-LOCK CONNECTION	PRICE
bar	psi						
ABSOLUTE PRESSURE							
0 to 0.34	0 to 5	PX309-005A5V	\$325	PX319-005A5V	\$325	PX329-005A5V	\$350
0 to 1	0 to 15	PX309-015A5V	245	PX319-015A5V	245	PX329-015A5V	295
0 to 2.1	0 to 30	PX309-030A5V	245	PX319-030A5V	245	PX329-030A5V	295
0 to 3.4	0 to 50	PX309-050A5V	245	PX319-050A5V	245	PX329-050A5V	295
0 to 6.9	0 to 100	PX309-100A5V	245	PX319-100A5V	245	PX329-100A5V	295
0 to 14	0 to 200	PX309-200A5V	245	PX319-200A5V	245	PX329-200A5V	295
0 to 21	0 to 300	PX309-300A5V	245	PX319-300A5V	245	PX329-300A5V	295
GAGE PRESSURE							
0 to 0.07	0 to 1	PX309-001G5V	\$345	PX319-001G5V	\$345	PX329-001G5V	\$370
0 to 0.14	0 to 2	PX309-002G5V	325	PX319-002G5V	325	PX329-002G5V	350
0 to 0.34	0 to 5	PX309-005G5V	300	PX319-005G5V	300	PX329-005G5V	325
0 to 1	0 to 15	PX309-015G5V	225	PX319-015G5V	225	PX329-015G5V	275
0 to 2.1	0 to 30	PX309-030G5V	225	PX319-030G5V	225	PX329-030G5V	275
0 to 3.4	0 to 50	PX309-050G5V	225	PX319-050G5V	225	PX329-050G5V	275
0 to 6.9	0 to 100	PX309-100G5V	225	PX319-100G5V	225	PX329-100G5V	275
0 to 10	0 to 150	PX309-150G5V	225	PX319-150G5V	225	PX329-150G5V	275
0 to 14	0 to 200	PX309-200G5V	225	PX319-200G5V	225	PX329-200G5V	275
0 to 21	0 to 300	PX309-300G5V	225	PX319-300G5V	225	PX329-300G5V	275
0 to 34	0 to 500	PX309-500G5V	225	PX319-500G5V	225	PX329-500G5V	275
0 to 69	0 to 1000	PX309-1KG5V	225	PX319-1KG5V	225	PX329-1KG5V	275
0 to 138	0 to 2000	PX309-2KG5V	225	PX319-2KG5V	225	PX329-2KG5V	275
0 to 207	0 to 3000	PX309-3KG5V	225	PX319-3KG5V	225	PX329-3KG5V	275
0 to 345	0 to 5000	PX309-5KG5V	225	PX319-5KG5T	225	PX329-5KG5V	275
0 to 517	0 to 7500	PX309-7.5KG5V	225	PX319-7.5KG5V	225	PX329-7.5KG5V	275
0 to 690	0 to 10,000	PX309-10KG5V	225	PX319-10KG5V	225	PX329-10KG5V	275

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
CAL-3	150.00	Recalibration: 5-point NIST traceable
PT06V-10-6S	26.50	Mating twist-lock connector for PX329
CA-39-4PC22-5	90.00	Mating twist-lock connector with 1.5 m (5') cable for PX329
CX5302	15.00	Extra mating mini DIN connector for PX319

1/4 NPT Pressure Snubbers: \$12.75
PS-4G = Gas
PS-4E = Lt Oil
PS-4D = Dense Lq

Comes complete with 5-point NIST-traceable calibration.

Ordering Examples: PX309-100G5V, 100 psi gage pressure transducer with 0 to 5 Vdc output and 1 m cable termination, \$225.

PX319-015A5V, 15 psi absolute pressure transducer with 0 to 5 Vdc output and mini DIN termination, \$300. PX329-3KG5V, 3000 psi gage pressure transducer with 0 to 5 Vdc output and twist-lock termination, \$275. Mating connector sold separately; order PT06V-10-6S, \$26.50.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters