


OMEGALABEL® Temperature Monitors

Series 21
\$66
All Models



Fast, Easy-To-Use Temperature Monitoring System

OMEGALABEL® is a self-adhesive temperature monitor consisting of a heat-sensitive indicator sealed under a transparent heat-resistant window. The indicator circle turns to light gray or black at the temperature rating shown on the card. Color change is not reversible and provides a temperature history of the surface being monitored. To serve as a permanent record, the OMEGALABEL® can be removed and attached to an inspection report.

Guaranteed Accuracy and Reliability

OMEGALABEL® accuracy is guaranteed to be within $\pm 2\%$.

The Series 21 OMEGALABEL® is conveniently mounted on sheets (21 per sheet) for fast, on-the-spot application by just peeling them off one at a time. The adhesive backing easily adheres to any clean, dry surface.

Requirements Estimator

Packs	Sheets	Labels
1 Pack	10	210
3 Packs	30	630
5 Packs	50	1050
10 Packs	100	2100
20 Packs	200	4200
30 Packs	300	6300
50 Packs	500	10500

MOST POPULAR MODELS HIGHLIGHTED!

OMEGALABEL® Series 21 Temperature Ranges			
Model No.	Range	Model No.	Range
21-100	38°C (100°F)	21-220	104°C (220°F)
21-110	43°C (110°F)	21-230	110°C (230°F)
21-120	49°C (120°F)	21-240	116°C (240°F)
21-130	54°C (130°F)	21-250	121°C (250°F)
21-140	60°C (140°F)	21-260	127°C (260°F)
21-150	66°C (150°F)	21-270	132°C (270°F)
21-160	71°C (160°F)	21-280	138°C (280°F)
21-170	77°C (170°F)	21-290	143°C (290°F)
21-180	82°C (180°F)	21-300	149°C (300°F)
21-190	88°C (190°F)	21-400	204°C (400°F)
21-200	93°C (200°F)	21-500	260°C (500°F)
21-210	99°C (210°F)		

Ordering Example: 21-500, 1 pack of labels with a temperature range of 260°C (500°F), \$66.

Notes: All temperatures can be combined for quantity pricing.
Dot dimension: 4.8 mm (3/16") diameter.
Individual label: 12 mm (1/2") square.
Standard packaging: 10 sheets of one temperature per pack.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters