

Adjustable Depth Thermocouples

TWO STYLES!

ANSI color code shown

To order IEC color code see page A-9

- Locking Fitting Freely Adjustable Over Flexible Armor
- Spring-Action Catch Holds Probe Firmly in Place

TYPE ADF
Fixed Locking Cap Becomes a Permanent Part of Your Installation



Extra Locking Fittings Available

\$10 Each

This unique thermocouple is easy to adjust to ANY immersion depth into wells (but NOTE: this probe cannot be immersed in liquids). Adjustable depth eliminates the need to stock a variety of fixed depth immersion probes. The locking cap can be positioned anywhere along the flexible armor and obtains its locking force from a unique spring-action catch. The welded stainless steel

tipped probe is held against the bottom of the well by compression of the armor.

Two styles are available. Style ADF has a unique locking fitting that mounts permanently to your equipment. The quick release action of the locking fitting allows fast installation and removal of the probe.


Style ADR has a removable locking fitting and requires a BTA adaptor. This style is ideal for installations where the mounting surface is under a layer of insulation, or where the locking cap must be removable.

MOST POPULAR MODELS HIGHLIGHTED!


To Order (Specify Model Number)			
Model Number	Termination Style	Price	
		Grounded Junction	Ungrounded Junction
ADR-(1)-(2)-(3)-(4)-1	1	\$27	\$33
ADR-(1)-(2)-(3)-(4)-2	2	35	41
ADR-(1)-(2)-(3)-(4)-3	3	39	45
ADF-(1)-(2)-(3)-(4)-1	1	\$29	\$35
ADF-(1)-(2)-(3)-(4)-2	2	37	43
ADF-(1)-(2)-(3)-(4)-3	3	41	47

TYPE ADR
Removable Locking Cap Bayonet Fitting Connects with a Twist

Detailed Dimensions ADR




Detailed Dimensions ADF



Design subject to change as engineering improvements permits.

Termination Styles



How to Order

Box 1: Specify Calibration: J, K, T or E

Box 2: Specify Junction: G (grounded) or U (ungrounded)

Box 3: Specify "A" Dimension (up to 3")

Box 4: Specify "B" Dimension (up to 48"), over 48", add \$2.25/ft to probe price

Termination Styles:

- 1 – Spade Lugs
- 2 – Male Quick Disconnect Type OST
- 3 – Female Quick Disconnect Type OST

Ordering Example: ADR-J-G-1/2-12-2, \$35.
Removable locking cap probe, Type J, grounded junction, 0.5" A dimension, 12" B dimension, male quick disconnect termination.

Standard size connectors.

Specify: ADR-LF or ADF-LF

Discount Schedule

1-10 Units Net
11-24 Units5%
25-49 Units10%
50 Units or more15%



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters