

# Compact, Economical Temperature Controllers


CCD101N Series

**\$39**

All Models



- ✓ Low Cost
- ✓ Heavy-Duty Switch
- ✓ Only 30 mm (1.2") Tall



CCD101N-050, \$39, shown actual size.

## Applications

The CCD101N temperature controllers are weatherproof remote control thermostats for individual circuits. They feature a temperature-sensitive bimetal disk in an epoxy-sealed housing. On reaching the non-adjustable calibrated setpoint, the disk activates a plunger, causing the heavy-duty switch contacts to open. The CCD101N is normally used as an across-the-line switch, but it may be used to operate contactor coils and other similar devices.

The CCD101N can also be used to operate external alarm devices or as a limit controller in conjunction with other CCD Series thermostats.

## Specifications

**Switch:** CCD101N, SPDT

**Switch Rating:** 25 A, 277V max

**Maximum Exposure Temperature:** 105°C (220°F)


**Minimum Exposure Temperature:** -40°C (-40°F)

**Leads:** 14 AWG copper—1.2 m (48") L

**Housing:** Plenco phenolic with annealed 304 SS mounting flange; epoxy resin seal protects switch from dirt and moisture

**FM Approvals for These Locations:** Class I, Division 2, Groups B, C and D; Class II, Division 2, Groups F and G; Class III, Division 2

**Attachment to Pipe:** 2 pipe clamps are required to attach controller to pipe (see ordering table)



**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)			
Model Number	Price	Open Setpoint (°F)	Close Setpoint (°F)
CCD101N-050	\$39.00	50 ±5	35 ±5
CCD101N-060	39.00	60 ±5	45 ±5
CCD101N-075	39.00	75 ±5	60 ±5
CCD101N-105	39.00	105 ±5	90 ±5
CCD101N-200	39.00	200 ±5	185 ±5
CCDPS-2	2.50	Adjustable pipe straps from 2 to 6"	

Comes complete with operator's manual.

**Ordering Examples:** CCD101N-075, compact, economical temperature controller, \$39. CCD101N-105, compact, economical temperature controller, \$39.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters