

Panel Punches and Hole Saws for Thermocouple Connectors, DIN-Size Controllers, and Panel Meters

DIN-Size Panel Punches

- ✓ 1/32, 3/64, 1/16, 1/8 Square, 1/8 and 1/4 DIN Sizes
- ✓ Will Accept Any Standard DIN-Size Controllers and Panel Meters
- ✓ Will Cut a Clean Hole in Up to 11 Gage (0.090) Aluminum or Up to 14 Gage (0.075) Mild Steel

DPP Series Starts at **\$400**



Rectangular Hole Punches

- ✓ Rugged Industrial Design
- ✓ Square Corners
- ✓ Sizes to Mount All OMEGA® Connectors
- ✓ Keyed Design Ensures Alignment of Punch and Die. Simply Drill a Pilot Hole and Punch Out the Exact Shape for the Connector.
- ✓ Will Cut a Clean Hole in Up to 14 Gage (0.078) Aluminum or up to 16 Gage (0.062) Mild Steel

CP Series Starts at **\$120**



Round Hole Punches

- ✓ No Reaming or Filing
- ✓ 6.35 mm (1/4") or 9.52 (3/8") Pilot Hole
- ✓ Exact Size for RMJ and RSJ Connectors

DIN-Size Panel Punches

RHP Series Starts at **\$58**



Hole Saws

- ✓ For Panels Over 3 mm (1/8") Thick
- ✓ Replaceable Blades
- ✓ 6.35 mm (1/4") Pilot Drill

With a hand drill or drill press, you can use these panel punches and hole saws to make jack panels. When a plate is too thick for punches, saws should work. Complete assembly requires saw, pilot drill, and mandril.



RHS Series Starts at **\$19**

Replacement Saws for RHS Series Saws



RS Series Starts at **\$16**

■ MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model Type	Model No.	Cutout Dimensions mm (in)	Designed For	Price	Pilot Hole mm (in)
Rectangular Connectors	CP-1	8.1 x 16.8 (0.318 x 0.661)	SMP, SMPW	\$120	6.35 (1/4)
	CP-2	9.5 x 16.7 (0.375 x 0.656)	NMP	120	7.9 (5/16)
	CP-3	13.5 x 26.2 (0.531 x 1.031)	OSTW, OGP NOX, USTW	120	9.5 (3/8)
	CP-4	13.1 x 36.8 (0.516 x 1.450)	OTP	120	9.5 (3/8)
	CP-5	16.1 x 30.4 (0.635 x 1.195)	JP, SJP	120	9.5 (3/8)
	CP-6	16.1 x 41.4 (0.635 x 1.630)	TPJ	120	9.5 (3/8)
	CP-7	16.4 x 26 (0.646 x 1.024)	NHX	120	9.5 (3/8)
	CP-8	9.9 x 19.4 (0.390 x .765)	SHX	120	6.35 (1/4)
DIN Size Panel Punches	DPP-1	22.5 x 45 (0.886 x 1.772)	1/2 DIN	\$400	12.7 (1/2)
	DPP-2	22.5 x 68 (0.886 x 2.677)	3/4 DIN	425	12.7 (1/2)
	DPP-3	22.5 x 92 (0.886 x 3.622)	1/2 DIN	450	12.7 (1/2)
	DPP-4	45 x 45 (1.772 x 1.772)	1/8 DIN Sq.	475	19 (3/4)
	DPP-5	45 x 92 (1.772 x 3.622)	1/8 DIN	525	19 (3/4)
	DPP-6	92 x 92 (3.622 x 3.622)	1/4 DIN	575	19 (3/4)
Round Connectors	RHS-43	43 (1 1/16) Dia.	CN77R3 & R5 Panel Meters	\$19	6.35 (1/4)
	RHS-58	15.87 (0.625) Dia.	RMJ	20	6.35 (1/4)
	RHS-78	22.22 (0.875) Dia.	RSJ	20	6.35 (1/4)
	RHP-58	15.87 (0.625) Dia.	RMJ	58	9.5 (3/8)
	RHP-78	22.22 (0.875) Dia.	RSJ	58	9.5 (3/8)
Replacement Saws	RS-58	15.87 (0.625) Dia.	RMJ	\$16	—
	RS-78	22.22 (0.875) Dia.	RSJ	16	—



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters