

Protective Carrying Cases

Hard-Sided, Leather and Vinyl Sleeve Varieties

Visit omega.com/cases for More Information on Omega's Wide Selection of Quality Instrument Cases!

130001
\$205



SC-530
\$65



SC-531, SC-540
\$65



RCC-1100
\$85



RCC-200A
\$42



RCC-6500
\$40



SC-83
\$30



RCC-1000
\$40



SC-600
\$20



SC-HH11A
\$15



SC-HHM20
\$15



SC-50
\$13



SC-300A
\$12⁵⁰



SC-HH500
\$15



SC-560
\$12





AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Dimensions (in) H x W x D	Description
130001	\$205.00	13 x 18 x 6	Zero aluminum case with combo lock
SC-530	65.00	8 x 4.5 x 1.75	Soft case with belt loop and shoulder strap
SC-531	65.00	5.75 x 3.5 x 2.5	Soft case with belt loop
SC-540	65.00	5.5 x 3.75 x 2.75	Soft case with belt loop
RCC-1100	85.00	17 x 12 x 5.5	Rugged carrying case with foam insert
RCC-200A	42.00	14 x 10 x 3.5	Rugged carrying case with foam insert
RCC-6500	40.00	8.5 x 5.5 x 2.5	Soft leather case with belt loop and shoulder strap
SC-83	30.00	5.25 x 2.25 x 1	Soft case with belt loop
RCC-1000	40.00	12.5 x 9 x 4.5	Rugged carrying case with foam insert
SC-600	20.00	9 x 6.5 x 1.25	Soft case with belt loop
SC-HH11A	15.00	9 x 2.5 x 1.5	Soft case with belt loop and mounting magnet
SC-HHM20	15.00	9 x 4 x 1.75	Soft case with belt loop
SC-50	13.00	7.25 x 3.75 x 1.25	Soft case with belt loop
SC-300A	12.50	4 x 5 x 3.25	Soft case with belt loop
SC-450L	18.00	9.25 x 3.25 x 1.75	Soft case with belt loop and hook
SC-560	12.00	7 x 2 x 1.5	Gun-style holster case with belt loop
SC-HH500	15.00	8.25 x 2.75 x 3.75	Soft case with belt loop
SC-450S	10.00	6 x 3 x 1.5	Soft case with belt loop and hook
SC546	10.00	6.5 x 2 x 1	Soft case
SC67	10.00	5 x 2 x 1	Soft case
SC737	10.00	5.25 x 3.75 x 1.5	Soft case with shoulder strap and belt clip
SC74	10.00	5.75 x 2 x 1	Soft case
SC-800	10.00	7 x 3.5 x 2.25	Soft case with belt loop
SC-HHLM3	10.00	6 x 2 x 0.75	Soft case
SC-SM	12.00	8.5 x 3.5 x 2.5	Soft case with belt loop

Ordering Example: 130001, zero aluminum case with combo lock, \$205.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters