

General-Purpose, Thermometers

Economical, Ideal for School and Laboratory Applications!

GT-736570, \$6.

GT-736590, \$6.50.

GT-737680, \$8.

GT-736000 Starts at **\$5**

Purchase in Quantity for Even Better Prices. See Discount Schedule Below.

All models shown actual size.

- ✓ Red Liquid-Filled Models
- ✓ Partial and Total Immersion Styles
- ✓ 305 mm (12") and 150 mm (6") Lengths
- ✓ Variety of Single and Dual Temperature Ranges

Perfect Where Glass Thermometers are Purchased Frequently!

Economical glass-bulb thermometers are ideal for school and laboratory applications. These general-purpose, easy-to-read white back units are available with red liquid filling, in a variety of ranges and styles.



Available with red safety liquid, in a variety of ranges and styles.

| Discount Schedule for Economical Thermometers | |
|---|-----|
| 11 to 24 Units | 10% |
| 25 to 49 Units | 15% |
| 50 to 99..... | 20% |

MOST POPULAR MODELS HIGHLIGHTED!

| To Order (Specify Model Number) | | | | |
|---|-----------------------------|----------------|-------------|--------|
| Model No. | Range | Length mm (in) | Div | Price |
| Red Organic Safety, White Back, Partial Immersion Calibrated at 76 mm | | | | |
| GT-736570 | -20 to 110°C | 305 (12) | 1° | \$6.00 |
| GT-736580 | -20 to 150°C | 305 (12) | 1° | 7.00 |
| GT-737000 | 0 to 230°F | 305 (12) | 2° | 6.00 |
| GT-736780 | -20 to 110°C/ 0 to 230°F | 305 (12) | 1°C/ 2°F | 8.00 |
| Red Organic Safety, White Back, Total Immersion | | | | |
| GT-736590 | -20 to 110°C | 305 (12) | 1° | \$6.50 |
| GT-736600 | -20 to 150°C | 305 (12) | 1° | 7.00 |
| GT-737680 | -20 to 110°C/ 0 to 230°F | 305 (12) | 1°C/ 2°F | 8.00 |
| Low Range Red Organic Safety, White Back, Total Immersion | | | | |
| GT-736620 | -50 to 50°C | 305 (12) | 1° | \$7.00 |
| Student Red Organic Safety, Partial Immersion Calibrated at 76 mm | | | | |
| GT-736630 | -10 to 110°C | 150 (6) | 1° | \$5.00 |
| GT-738640 | -10 to 110°C/ 0 to 230°F | 150 (6) | 1°C/ 2°F | 6.00 |

Comes complete in a protective plastic shipping tube.

Ordering Example: GT-737680, dual range [-20 to 110°C (0 to 230°F)] total immersion, red safety thermometer, \$8.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters