

Economical Thermocouple Calibrator Source

HH20CAL
\$169



- ✓ Inexpensive, Accurate Calibrations
- ✓ Simulate J, K and T Thermocouples
- ✓ Compatible with Wide Variety of Handhelds
- ✓ Accurate to 0.3% of Rdg
- ✓ Up to 0.1° Resolution

The HH20CAL is a compact device that plugs onto a handheld thermocouple thermometer, turning it into a high accuracy thermocouple calibrator. Simply turn the vernier dial on the HH20CAL so that the handheld meter indicates the desired temperature; the user can then calibrate transmitters, panel meters, controllers, or other thermocouple instruments.

The HH20CAL can be used with a wide variety of OMEGA® handheld indicators. The swing-out back support gives extra strength for top-mount units, and swings up to give clearance for front connector units. The male connector on the HH20CAL is fitted with a 2-position slide and is compatible with both single and dual input thermometers.

Specifications

Accuracy: 0.3% rdg +1°C, plus accuracy of indicating thermometer; includes ambient temperature effect

Simulation Output Temperature

Range: -350 to 1372°C
(-350 to 2500°F), overall

Low Range: -212 to 121°C
(-350 to 250°F);

Med Range: 93 to 649°C
(200 to 1200°F);

High Range: 649 to 1371°C
(1200 to 2500°F)

Resolution: Allows tuning to 0.1°C; limited by indicating thermometer

Operating Ambient: 0 to 54°C
(32 to 130°F); less than 80% RH to 35°C (95°F)

Storage Temperature: -34 to 54°C
(-30 to 130°F); less than 80% RH to 35°C (95°F)

Power: 9V battery (included)

Battery Life: 1000 h, alkaline

Dimensions: 127 H x 71 W x 38 mm D
(5 x 2.8 x 1.5")

Weight: 0.23 kg (8 oz)



Plugs into Handheld Indicator!



HH20CAL, \$169, shown smaller than actual size.

HH-21A meter sold separately, \$175. See page L-28.

To instrument being calibrated.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HH20CAL	\$169	J/K/T economical calibrator
CL-300-CABLE-(*)-2	14	Calibration cable, 0.61 m (2'), PVC insulation, 24 AWG, SMP connector to spade lugs
CL-300-CABLE-(*)-10	27	Calibration cable, 3 m (10'), PVC insulation, 24 AWG, SMP connector to spade lugs
CL-300-RSC-(*)-2	20	Calibration cable, 0.61 m (2'), retractable cable, expands to 3 m (10'), SMP connector to spade lugs
MN1604	3	Replacement 9V battery

Comes complete with 9V alkaline battery and operator's manual.

* Specify calibration: J, K, or T.

Ordering Example: HH20CAL, thermocouple calibrator, CL300-RSC-J-2, 0.61 m (2') retractable cable, for Type J thermocouples, \$169 + 14 = \$183.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters