

Digital Thermometers with Multifunction Features

HH81A Series
Starts at
\$149



- ✓ **Wide Measurement Range:**
-200 to 1372°C (-328 to 2501°F)
- ✓ **Stores up to 10 Readings**
- ✓ **Auto Power-Off**
- ✓ **Single and Dual Input Models**
- ✓ **Data Hold Function**
- ✓ **Min/Max Record Function**
- ✓ **Resolution 0.1°C/0.1°F**

The HH81A and HH82A handhelds are an economically priced digital thermometers. These units are portable and easy to use. They are fully programmable input models for K, E, J, and T type thermocouples. The standard features include min/max reading, reading hold, both are °C to °F switchable and can store up to 10 readings by the press of a button.

Specifications

Measuring Range (only the main unit)

Thermocouple Type:

Type K: -200°C to 1372°C (-328°F to 2501.6°F)

Type E: -200°C to 700°C (-328°F to 1292°F)

Type J: -200°C to 1000°C (-328°F to 1832°F)

Type T: -200°C to 400°C (-328°F to 752°F)

Resolution: -200.0°C to 199.9°C; 0.1°C or 1°C (when 1°C resolution is set); 200°C or above: 1°C

Accuracy: -200.0°C to -100.1°C: $\pm(0.1\% \text{ of rdg} + 1.0^\circ\text{C})$;
-100.0°C to 199.9°C: $\pm(0.1\% \text{ of rdg} + 0.7^\circ\text{C})$; +200°C or above, or when 1°C resolution is set: $\pm(0.2\% \text{ of rdg} + 1^\circ\text{C})$

Measurement Interval: Approx 1 second (1-channel measurement); approx 2 seconds (2-channel measurement)

Data Storage: Capable of storing up to 10 measured data items

Simplified Correction: Correction range: $\pm 20^\circ\text{C}$ of measured value

Display Items: HOLD, RCD, REL, ADJ, MAX, MIN, MEM, °C; TC Type K, J, E, T, battery alarm, chA, chB, chA-chB (HH82A only)

Other Functions: Auto power-off, battery alarm

Operating Temperature and Humidity: 0°C to 50°C, 20 to 80% RH (no condensation)

Power Requirements: 2 "AA" alkaline dry batteries (included) (LR6)

Battery Life: About 450 hours

Construction: Conforms to IP54 (dust-proof and drip-proof requirements of IEC529)

Dimensions: Approx 151 H x 56 W x 33 mm D (5.9" x 2.2" x 1.3") (excluding protrusions)

Weight: Approx 180 g (6.3 oz) (including batteries)

Connector: SMP Type



HH82A, \$224, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model	Price	Description
HH81A	\$149	1-channel multifunction thermometer
HH82A	224	2-channel multifunction thermometer
Accessories		
HH-NIST*	\$55	NIST-traceable calibration, no points
CAL-3-HH	75	NIST-traceable calibration, with points
WPC-80	25	Waterproof cover
SC-800	10	Soft carrying case w/belt loop

Comes with Type K beaded wire thermocouple (1 per channel), 2 "AA" batteries, operator's manual.
Ordering Example: HH82A dual input thermometer, \$224.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters