

DMM/Thermometer with AC Clamp Feature

HHM59
\$139



- ✓ **Measures**
 - Current to 1000 A AC
 - Voltage to 750 Vac, 1000 Vdc
 - Resistance to 2 MΩ
- ✓ **Direct Temperature Readout for Type K Thermocouple**
- ✓ **51 mm (2") Jaw Opening**
- ✓ **Peak Hold Feature Captures Current Surges**

The HHM59 is a lightweight completely portable digital clamp meter with a 3½ digit LCD display which is readable in all light conditions. The decimal point is automatically positioned, and the polarity indication is standard for negative readings. Overrange and low battery indications are also standard.

Specifications

General

Display: 3½ digit liquid crystal; 1999 maximum reading
Overrange Indication: Blanking of all digits except the MSD, decimal point and polarity sign (if negative)
Low Battery: "LO BAT" displayed
Measurement Rate: 3 measurements per second, nominal
Operating Temperature: 0 to 50°C, 0 to 70% RH
Storage Temperature: -20 to 60°C, 0 to 80% RH with battery removed
Power: 9V battery (included)
Battery Life: 100 hours typical
Weight: 0.31 kg (11 oz) including battery
Dimensions: 229 H x 69 W x 38 mm D (9 x 2.7 x 1.5")

DC Voltages

Range: 200 mV, 20V, 1000V
Accuracy: 0.5% of rdg +1 digit
Input Impedance: 10 MΩ
Overload Protection: 500 Vdc, 350 Vac (15 sec, 2V range); 1200 Vdc, 850 Vac (all other ranges)
Resolution: 100 mV (200 mV range), 10 mV (20V range), 1V (1000V range)

Resistance

Ranges: 200 Ω, 20 kΩ, 2 MΩ
Accuracy: 200 Ω, 1% of rdg + 3 digits; 2 kΩ through 2 MΩ, 0.8% of rdg + 1 digit



HHM59, \$139.

Overload Protection: 500 Vdc/Vac
Resolution: 0.1 Ω (200 Ω range), 10 Ω (20 kΩ range), 1 kΩ (2 MΩ range)

AC Voltages

Ranges: 200V, 750V
Accuracy: 1.2% of rdg + 10 digits; 50 to 500 Hz
Input Impedance: 10 MΩ
Overload Protection: 1200 Vdc, 850 Vac
Resolution: 0.1V (200V range) 1V (750V range)

Temperature

Ranges: -40 to 750°C, -40 to 1400°F
Resolution: 0.1°C/°F
Accuracy: 3% of reading + 1°C, 2°F

AC Current

Ranges: 20 A, 200 A, 1000 A

Free

Thermocouple Included!

The HHM59 includes a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy.

Order a Spare! Model No. SC-GG-K-30-36, \$15.

Accuracy (50 to 500 Hz):

20 A: 3% of rdg + 5 digits
200 A: 2% of rdg + 5 digits
200 A to 800 A: 2% of rdg + 5 digits
800 A to 1000 A: 3% of rdg + 5 digits

Overload Protection: 1200 A for 60 sec

Jaw Opening: 5 cm (2")

Resolution: 10 mA (20 A range), 100 mA (200 A range), 1 A (1000 A range)

Instant Continuity

Response Time: 100 msec

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HHM59	\$139	Digital clamp meter

Comes complete with wrist strap, 9V battery, carrying case with strap, test leads, Type K beaded wire thermocouple and operator's manual.

Ordering Example: HHM59, digital clamp meter, \$139.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters