

Stick-Type Portable MegOhmMeter

HHM65
\$109



- ✓ Portable, Simple One Hand Operation
- ✓ Range from 20/2000 MΩ
- ✓ Meter with Backlit LCD Display
- ✓ 3½ Digit 1999 Count Resolution
- ✓ Accuracy: 20 MΩ ± (2% rdg + 2 digits); 2000 MΩ ± (4% rdg + 2 digits); >500 MΩ ± (5% rdg + 2 digits)
- ✓ Provides 500V to Test Insulation
- ✓ Valox® Housing to Withstand Impacts
- ✓ Smallest Insulation Tester
- ✓ External Power Supply Input Jack (6 Vdc)
- ✓ Battery: 4 pcs 1.5V ("AAA" Size) Included (MN2400)
- ✓ Auto Hold, Auto Power-Off
- ✓ Dimensions: 170 H x 43 W x 41 mm D (6.7 x 1.7 x 1.6")
- ✓ Weight: 180 g (6.3 oz)



Test leads included.



HHM65, \$109, shown actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HHM65	\$109	MegOhmMeter

Comes complete with soft vinyl carrying case, 4 "AAA" batteries, test leads and operator's manual.

Ordering Example: HHM65, MegOhmMeter, \$109.

Accessory

Model No.	Price	Description
MN2400	\$3	Spare "AAA" alkaline battery

Recommended Reference Book: Dictionary of Electronics, EE-1068, \$27, See Section Y for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters