

Classic Handheld Analog VOM

HHMA
Starts at
\$86



- ✓ Drop Resistant High-Impact Case
- ✓ Diode Overload Protection Meter
- ✓ Fused Resistance Ranges
- ✓ AC/DC Voltage Measurement to 1200V

Specifications

DC Voltage

Ranges: 3, 12, 60, 300, 1200 (20 kΩ/Volt)
Accuracy: ±3% of full scale

AC Voltage

Ranges: 3, 12, 60, 300, 1200 (5 kΩ/Volt)
Accuracy: ±4% of full scale

Resistance

Ranges: 20 kΩ, 200 kΩ, 2 MΩ, 20 MΩ
(200 Ω center scale on lowest range)

Accuracy: ±3% of scale length

DC Current

Ranges: 600 μA, 6 mA, 60 mA, 600 mA

Burden Voltage: 330 mV

Accuracy: ±3% of full scale

Weight: 1 kg (2 lb)

Dimensions: 70 W x 34 D x 108 mm L

(2 3/4 x 1 5/8 x 4 1/4")

**Old Favorite
Tried and True.**

HHMA-1, \$86.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
HHMA	\$86	Analog VOM
HHMA-CP	55	AC clamp on current probe (not pictured)
HHMA-TL	9	1/2" test leads with alligator clips (spare)
HHMA-SC	11	Soft case
HHMA-BATT	5	Replacement battery set (12V, 1.5V 1 of each)

Comes complete with manual, battery set and test lead set.

Ordering Examples: HHMA, HHMA-CP and HHMA-SC, analog VOM, AC clamp-on current probe and a soft case: \$86 + 55 + 11 = \$152. OCW-2 OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$25), \$86 + 25 = \$111.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Sound Level Meter

HHSL-1
\$145



- ✓ Portability and Simplicity One Hand Operation
- ✓ AC and DC Output Functions Provided
- ✓ A and C Frequency Weighting Characteristics
- ✓ Slow and Fast Time Frequency Weighting Characteristics
- ✓ Maximum Hold Function
- ✓ Under and Over Range Indication
- ✓ Valox Housing to Withstand Accidental Drops

Specifications

Display: 3 1/2 digit liquid crystal display (LCD) with maximum reading of 1999
Zero: Automatic

Low battery indication: The is displayed when battery voltage drops below the operating level

Operating environment:

0 to 50°C at <75% RH

Storage temperature:

-20 to 60°C, 0 to 80% RH with battery removed from meter

Accuracy:

Stated accuracy at 23°C ±5°C, <75% RH

Dimensions: 215 H x 44 W x 40 mm D (8.5 x 1.7 x 1.6")

Weight: 200 g including battery (7 oz) (1.5V x 4 pcs "AAA" size)

Standard Applied: IEC 651 Type 2

Range:

Lo: 35 to 90 dB

Hi: 75 to 130 dB

Resolution: 0.1 dB

Accuracy: ±1.5 dB

(ref 94 dB @ 1 kHz)

Dynamic Range: 55 dB

Frequency Range:

31.5 to 8000 Hz

Frequency Weighting: A, C

Time Weighting: Slow & Fast

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
HHSL-1	\$145	Sound level meter
STICK-CABLE	9	Analog output cable

Comes complete with operator's manual, 4 "AAA" alkaline batteries, sound shield, and soft carrying case. Ordering Example: HHSL-1 and STICK-CABLE, sound level meter and analog output cable, \$145 + 9 = \$154.

HHSL-1, \$145.
Soft carrying case included.



Maximum Hold: Decay <1 dB/3min

Microphone: Electret condenser microphone

Auxiliary Outputs

AC Conditioned:

0.55 Vrms

corresponding to each range step

Impedance: 600 Ω

DC Conditioned:

10 mV/dB (nominal)

Impedance: 100 Ω



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters