

Economical Handheld Digital Tachometer with RS232C Software*

OMEGAETTE™
Moderately Priced
Instruments. Ideal for
Education, Training
and Demonstration
Programs.

- ✓ 5 Digit LCD Display
- ✓ Light Reflex Measurement Technology
- ✓ Range 10.00 to 99,999 RPM
- ✓ Measuring Distance 50 to 300 mm
- ✓ Event Counter with Elapsed Time (HH:MM)
- ✓ HHT-1502 Optional Contact Adaptor
- ✓ Max/Min/Hold: True Average
- ✓ Auto Range RPM
- ✓ RS232 Interface for Model HHT-1501
- ✓ Contact RPM and Circumferential Velocity (HHT-1502CA)

HHT-1500 Series
Starts at
\$195



The HHT-1500 Series is an accurate economical, non-contact optical digital tachometer. All units come complete with reflective tape and carrying case. An optional contact adaptor, HHT-1502CA is easy to attach and converts the unit to mechanical measurement. Users affix a tape on the shaft to be measured. The tachometer measures the time between reflected pulses of light and calculates the RPM.

Specifications

Speed (Optical)

	Range	Resolution	Accuracy
RPM	10.00 ~ 99999	0.01/0.1/1	0.04% ± 2 dgts
rps(Hz)	0.200 ~ 2000.0	0.001/0.01/0.1	0.04% ± 2 dgts

Speed (Contact)

	Range	Resolution	Accuracy
RPM / ("/" symbolizes "Contact")	10.00 to 29999	0.001/0.01/0.1/1	0.04% ± 2 dgts
m/min	1.000 to 2999.9	0.001/0.01/0.1	0.04% ± 2 dgts
ft/min	3.00 to 10000	0.001/0.01/0.1	0.04% ± 2 dgts
yard/min	1.00 to 3000	0.001/0.01/0.1	0.04% ± 2 dgts

General Specifications

External TTL Input	High > 4.5V (HHT-1501)
Display	5 digits 99999 counts
Sampling Rate	0.7 second (> 60 rpm) > 1 second (10 to 60 rpm)
Measuring Distance	50 to 300 mm (2 to 12")
Time Base	4.0 MHz Quartz Crystal
Range Selection	Automatic
Battery	Four 1.5 V "AA" (included)
Auto Power-Off	30 minutes
Operating Temp	0 to 50°C (32 to 122°F)
Size	72 L x 63 W x 36 mm D (6.8 x 2.5 x 1.5")
Weight	190 g (6.7 oz.) (including battery)

HHT-1500,
\$195, shown
actual size.



Event Counter

Range	Max Input Frequency
0 to 99999	10 KHz with 5% duty cycle

ALL MODELS AVAILABLE FOR FAST DELIVERY!

* HHT1501 only.
Comes complete with carrying case, reflective tape, 4 "AA" alkaline batteries and operator's manual.
Ordering Example:
HHT-1501, digital tachometer with RS232C cable and software and HHT-1502CA, contact adaptor, \$225 + 45 = \$270.

To Order (Specify Model Number)		
Model No.	Price	Description
HHT-1500	\$195	Digital tachometer
HHT-1501	225	Digital tachometer with RS232C cable and software
HHT-1502CA	45	Optional contact adaptor



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters