


# Mica-Glass Insulated Ultra High Temperature Heater Hook-Up Wire

HTMG Series  
Starts at  
**\$1**  
Per Foot



- ✓ 450°C (842°F) Temperature Rating
- ✓ CSA Certified, NRTL and UL Listed
- ✓ Single Stranded 27% Nickel Coated Copper Conductor
- ✓ Mica Tape Insulation with Treated Glass Overbraid



HTMG high-temperature lead wires are designed for appliances and industrial heating products—such as commercial food service equipment, heaters, heat treating furnaces, kilns, heater elements and other applications up to 450°C (842°F).

Discount Schedule	
50 to 99 ft. ....	10%
100 to 199 ft. ....	15%
200 to 499 ft. ....	20%
499 ft. and up .....	25%

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)						
Gage	Model No.	Type Price/ft	Stranded	Volts	Nominal OD mm (in)	Approx Wt kg/300 m (lb/1000')
22	HTMG-1CU-322S/C	\$1.00	7 x 30	300	2.0 (0.08)	2.5 (5.5)
22	HTMG-1CU-622S/C	1.45		600	2.6 (0.10)	3.2 (7.0)
20	HTMG-1CU-320S/C	1.35	10 x 30	300	2.1 (0.08)	3.2 (7.0)
20	HTMG-1CU-620S/C	1.65		600	2.8 (0.11)	4.1 (9.0)
18	HTMG-1CU-318S/C	1.45	16 x 30	300	2.4 (0.10)	4.3 (9.5)
18	HTMG-1CU-618S/C	1.85		600	3.0 (0.12)	5.2 (11.5)
16	HTMG-1CU-316S/C	1.85	26 x 30	300	2.7 (0.11)	5.9 (13.0)
16	HTMG-1CU-616S/C	2.25		600	3.3 (0.13)	6.8 (15.0)
14	HTMG-1CU-314S/C	2.45	41 x 30	300	3.0 (0.12)	8.4 (18.5)
14	HTMG-1CU-614S/C	2.90		600	3.7 (0.14)	9.5 (21.0)
12	HTMG-1CU-312S/C	3.35	65 x 30	300	3.5 (0.14)	12.2 (27.0)
12	HTMG-1CU-612S/C	3.85		600	4.1 (0.16)	13.4 (29.5)
10	HTMG-1CU-310S/C	5.65	105 x 30	300	5.1 (0.20)	21.1 (46.5)
10	HTMG-1CU-610S/C	6.20		600	5.7 (0.22)	22.9 (50.5)
8	HTMG-1CU-308S/C	8.95	133 x 29	300	6.0 (0.23)	31.8 (70.0)
8	HTMG-1CU-608S/C	9.85		600	6.1 (0.26)	34.2 (75.5)

Standard Color: Natural (tan).

Ordering Example: HTMG-1CU-322S/C, 100' spool of 22 gage stranded wire, \$1.00 x 100 = \$100 (less 30% discount) = \$70. See heater hook-up wire introduction for current carrying capacity and derating.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters