

Quick-Connect Surface Probes

With Miniature Connectors, Retractable Cable, and Utility Handle



- ✓ J, K, T, and E Calibrations Available
- ✓ Fast Interchangeability
- ✓ 0.3 m (1') Retractable Cable Stretches to 1.5 m (5')



 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)			
Code	Model Number ANSI Color Code	Price	Description
A-G	TK-3-(†)	\$242	Quick-connect probe kit, includes all styles shown A-G
A	HYP5-21-1-1/2-(*)-G-SMPW	50	Hypodermic probe intended to be used for laboratory, industrial and natural science applications; needle: 38 x 0.79 mm (1.5 x 0.03"); tip rated to 200°C (400°F)
B	SMP-NP-(*)-125G-6	30	Penetration probe conical tip designed for penetration into semi-frozen objects; tip rated to 925°C (1700°F); 3 mm (1/8") diameter, 304 SS
C	SMP-RT-(*)-125G-6	40	Reduced-tip, fast-response probe; 3 to 1.5 mm (1/8" to 1/16") diameter at tip; tip rated for temperatures up to 925°C (1700°F)
D	SMP-AP-(*)-125E-6	50	Air probe; drilled end exposes bead to air flow for fast measurements; 4.5 mm (3/16") diameter shield and 1.5 mm (1/16") 304 SS tip rated to 260°C (500°F)
E	(*)MQSS-125G-6	24	General purpose immersion probe; 3 mm (1/8") dia., 304 SS tip rated to 260°C (500°F)
F	SMP-HT-(†)-6	50	Ceramic tip probe features a spring-loaded thermocouple to ensure consistent readings; tip rated to 650°C (1200°F)
G	88000-(*)-RSC-SMPW-M	25	Quick-connect handle with integral locking mechanism secures any miniature probe while in use

* Specify calibration as J, K, E or T.

† Specify calibration as J, K or E.

Ordering Examples: TK-3-K, quick-connect probe kit, includes all styles shown A-G and handle, \$242.

88000-K-RSC-SMPW, quick-connect Type K handle, SMP-RT-K-125G-6, reduced-tip, fast-response Type K probe, \$25 + 40 = \$65.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters