

DIN Rail Mounting Linear Power Supplies



PSDIN-41000R and
PSDIN-42000B Series
Starts at
\$72



- ✓ DIN Rail Mounting
- ✓ Low Ripple, Low Noise
- ✓ Isolated Input to Output
- ✓ LED Indicator for Power On

The PSDIN-41000R Series range of power supplies are designed for quick and trouble-free installation onto 35 mm profile DIN rails. With outputs ranging from 5 to 24V and maximum current capabilities from 100 to 500 mA, these units are ideal for most instrumentation and control systems. Every model in the range is provided with output current foldback limiting and is fully short-circuit protected. Great attention has been taken to usability and safety. The double insulated housing protects users without the need for earthing. A green "supply on" LED is provided to clearly indicate the presence of power, and link selection allows the use of 110 or 230V supplies without derating.

The PSDIN-42000B Series DIN rail mounting power supplies are supplied ready for connection. The unit has only to be snapped on to the 35 mm profile rail and connected to the clearly marked terminal screws. A status LED indicates power is on. For increased power two or more units may be connected in parallel. The output of these units is fully protected against short circuits and overload.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



PSDIN-41052R, \$72.

Both models shown smaller than actual size.



PSDIN-42024B3, \$315.

Specifications

Input: 115/230 Vac, 50/60 Hz

Voltage Output: See To Order chart (next page)

Ripple and Noise: 5 mV PK-PK max

Output Voltage Tolerance: $\pm 0.5\%$ max

Load Regulation: $\pm 0.05\%$ for 50% load change

Line Regulation: $\pm 0.05\%$ for 10% line change

Isolation: Input to output 3750 Vac min

Temperature Rating: Standard range 0 to 40°C (32 to 104°F) (full-rated, derated linearly to 40% at 70°C (158°F))

Case Size:

PSDIN-41000R Series:
119.2 L x 45 W x 73.2 mm H
(4.69 x 1.77 x 2.88")

PSDIN-42000B Series:
162 L x 105 W x 98 mm H
(6.38 x 4.13 x 3.86")

Case Material:

PSDIN-41000R Series: Polycarbonate
PSDIN-42000B Series: Steel housing with aluminum base

Weight:

PSDIN-41000R: 0.53 kg (19 oz)
PSDIN-42000B: 2.49 kg (88 oz)



TXDIN70, DIN rail temperature transmitter, \$85.



TXDIN70-DISPLAY, external plug-in display, \$20.

All models shown smaller than actual size.



TXDIN1620, \$219.

TXDIN1630, \$219.

TXDIN1610, \$219.



TXDIN101, \$260.

PSDIN-41000R Series

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)			
Model No	Price	Description	Voltage Output
PSDIN-41052R	\$72	DIN rail mounting linear power supply	5 Vdc, 200 mA
PSDIN-41055R	84	DIN rail mounting linear power supply	5 Vdc, 500 mA
PSDIN-41121R	72	DIN rail mounting linear power supply	12 Vdc, 100 mA
PSDIN-41122R	77	DIN rail mounting linear power supply	12 Vdc, 200 mA
PSDIN-41124R	84	DIN rail mounting linear power supply	12 Vdc, 400 mA
PSDIN-41151R	75	DIN rail mounting linear power supply	15 Vdc, 100 mA
PSDIN-41153R	84	DIN rail mounting linear power supply	15 Vdc, 300 mA
PSDIN-41241R	77	DIN rail mounting linear power supply	24 Vdc, 100 mA
PSDIN-41242R	84	DIN rail mounting linear power supply	24 Vdc, 200 mA
PSDIN-41245R	102	DIN rail mounting linear power supply	24 Vdc, 500 mA

Comes complete with operator's manual

Ordering Example: PSDIN-41242R, DIN rail mounting linear power supply 24 Vdc, 200 mA, RoHS compliant, \$84. OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years, (\$21) \$84 + 21 = \$105.

PSDIN-42000B Series

Model No	Price	Description	Voltage Output
PSDIN-42024B3	\$315	DIN rail mounting linear power supply	24 Vdc, 3 A
PSDIN-42024B4	323	DIN rail mounting linear power supply	24 Vdc, 4 A

Comes complete with operator's manual

Ordering Example: PSDIN-42024B3, DIN rail mounting linear power supply 24 Vdc, 3 A, \$315. OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years, (\$78) \$315 + 78 = \$393.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters