

8-Channel Portable Thermometer/Data Logger with SD Card Data Recorder

RDXL8
Starts at
\$1900



- ✓ 127 mm (5") Display
- ✓ 8 Configurable Isolated Inputs for Thermocouples and DC Millivolts
- ✓ SD Card, Real-Time Data Logger
- ✓ Graphic Display of Each Input
- ✓ Programmable Hi or Lo Alarm for 8 Inputs
- ✓ 2 GB SD Card and Software Included
- ✓ Built-In Calendar Clock
- ✓ USB Communication with PC for Downloading Data
- ✓ Stand-Alone Operation Through Graphical Display

The RDXL8 with its high resolution and fast analog to digital converter will meet the data logging requirements in most industrial applications. The ability to show measured values and to analyze them on its graphical display eliminates the need to download collected data to a computer for further analysis. The RDXL8 is the perfect choice for remote logging, and ideal for use as a mobile measuring device for the industrial environment. The RDXL8 series multipoint data logger is valuable in the industry because of their ability to perform integrated recording, profiling and archiving functions. They offer display versatility and flexible data storage.



Top view showing 8 isolated inputs.

RDXL8CD, \$2500.

Specifications

Battery Type:

RDXL8: Eight 1.5V "AA" alkaline batteries (included)

RDXL8CD: One 11.1V lithium battery (included)

AC Adaptor:

DC: Regulated 12V/300 mA output

AC: 110V

Power Consumption:

100 mA: With backlight

70 mA: Without backlight

Cold Junction

Compensation Accuracy:
±0.5°C/±0.9°F

Temperature Coefficient:

0.01% of FS/°C

Isolated Input Protection

Between Any Two Inputs:
350 Vp-p

Dimensions:

257 L x 155 W x 57 mm Dia
(10.1 x 6.1 x 2.2")

Weight: 1160 g (40.9 oz)
(with batteries)

Operation Environment:

0 to 50°C, 85% RH

Storage Environment:

-20 to 60°C, 75% RH



Input	Range °C	Accuracy °C	Range °F	Accuracy °F
K	-200 to -100	±2	-328 to -148	±3.6
	-100 to 999	±0.05% ±1	-149 to 999	±0.05% ±1.8
	1000 to 1370	±0.2% ±1	1000 to 2498	±0.2% ±1.8
J	-200 to -100	±2.5	-328 to -148	±4.5
	-100 to 100	±1.5	-148 to 212	±2.7
	100 to 999	±0.05% ±1	212 to 1832	±0.2% ±1
E	-150 to -100	±2	-238 to -148	±3.6
	-100 to 760	±0.05% ±1	-148 to 1400	±0.2% ±1
T	-200 to -100	±1.5	-328 to 148	±2.7
	-100 to 400	±0.1% ±0.5	-148 to 752	±0.1% ±0.9
R/S	0 to 100	±5	32 to 212	±9
	100 to 300	±3	212 to 572	±5.4
	300 to 999	±0.05% ±2	572 to 1000	±0.05% ±3.6
	1000 to 1600	±0.1% ±2	1000 to 2912	±0.1% ±3.6
N	0 to 999	±0.1% ±1	32 to 999	±0.1% ±1.8
	1000 to 1300	±0.2% ±1	1000 to 2372	±0.2% ±1.8
L	-200 to 900	±0.1% ±1	-328 to 1652	±0.2% ±1
U	0 to 600	±0.1% ±1	32 to 1112	±0.2% ±1
B	600 to 999	±0.05% ±2	1112 to 1831	±0.05% ±3.6
	1000 to 1760	±0.1% ±2	1832 to 3200	±0.1% ±3.6
C	0 to 999	±0.1% ±1.5	32 to 999	±0.1% ±2.7
	1000 to 1760	±0.2% ±1.5	1000 to 3200	±0.2% ±2.7
mV	-60 to 60	±60 uV	-60 to 60	±60 uV



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
RDXL8	\$1900	Multi-input thermometer/data logger, monochrome
RDXL8CD	2500	Multi-input thermometer/data logger, color version

Accessories

Model No.	Price	Description
RDXL800-PRINTER	\$440	Thermal printer for RDXL8 only
RDXL800CD-PRINTER	440	Thermal printer for RDXL8CD only
RDXL800-PAPER	18	Thermal paper (2 rolls)
2 GB-SD	10	Spare 2 GB SD card

Comes complete with (8) 1.5V "AA" alkaline batteries, AC adaptor, USB cable, software CD, SD card (2 GB), (8) Type K beaded wire thermocouples, carrying case and operator's manual.

Note: RDXL8 comes with (8) 1.5V "AA" alkaline batteries; RDXL8 CD comes with (1) 11.1V lithium battery.

Ordering Examples: RDXL8, multi-input thermometer/data logger, \$1900. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$350), \$1900 + 350 = \$2250.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters