



# Economical Humidity/ Temperature Sensor

## Features USB Interface and Free Recording and Logging Software

RH-USB  
**\$149**



Optional\*

- ✓ Connects Directly to a USB Port on Your Computer
- ✓ Free Software Converts Your PC into a Humidity and Temperature Meter, Data Logger or Chart Recorder
- ✓ Accurate to  $\pm 3\%$  RH,  $\pm 1^\circ\text{C}$  ( $\pm 1.8^\circ\text{F}$ )
- ✓ 316 SS Housing and Removable Stainless Steel Sensor Filter
- ✓ Suited for Wall or Duct Mounting

The RH-USB relative humidity/temperature sensor provides a reliable and economical method for most relative humidity and temperature monitoring applications. The compact design is ideal for wall or duct mounting. Each unit is factory calibrated to provide excellent sensitivity, fast response, and stability. The unit features a simple installation with a direct USB connection. The free user software converts your PC into both a humidity and temperature meter, chart recorder or data logger. The design features a 316 SS NEMA 4 (IP66) housing. A mounting kit is also available that allows for wall or duct mounting.



Laptop not included.

### Specifications

#### Temperature:

**Range:** -17 to 49°C (1 to 120°F)  
**Accuracy:**  $\pm 1^\circ\text{C}$  ( $\pm 1.8^\circ\text{F}$ )

#### Relative Humidity:

**Range:** 2 to 98% RH  
**Accuracy:**  $\pm 3\%$  RH (@ 15 to 90% RH)

**Repeatability:**  $\pm 1\%$  RH

**PC Interface:** USB

**USB Cable:** Integral to sensor, 2 m (6') (shielded) Type A plug

**Software (Included):** Requires Windows® 2000, XP, or Vista operating system

**Housing:** 316 stainless steel

**Dimensions:** 138 L x 16 mm D (5.5 x 0.625")

**Weight:** 67 g (0.18 lb)

RH-USB, \$149, shown smaller than actual size.

**Thermocouple Probe with USB Connection Available. See Model TJ-USB on page A-86**

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
RH-USB	\$149	Humidity temperature sensor with USB connection

### Accessories

Model No.	Price	Description
HX70-MKIT	\$15	Wall/duct mounting kit
CAL-3-HU*	125	NIST traceable calibration with 3 data points

Comes complete with an integral shielded 2 m (6') USB cable with Type-A connector, free software, removable protective sensor filter and operator's manual.

**Ordering Example:** RH-USB RH/temp sensor and HX70-MKIT wall/duct mounting kit, \$149 + 15 = \$164.



HX70-MKIT, \$15, wall/duct mounting kit, shown smaller than actual size.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters