

Meter Accessories

For the DP41, DP24, DP25, DP26, DPF50, DPF400, DPF701, DPF5100, PTC41, DP116, DP119 and the iSeries

Panel punches available, visit omega.com/panelpunches

BUMPER BAND® Color-Coded Protective Guards

Bumper Band® guards are made from a flexible material designed to provide additional moisture protection and protect against accidents. Available in 1/8 and 3/64 DIN sizes, Bumper Band® guards are compatible with DP40 Series and DP24, DP25, DP26, DP119 and DP116 Series meters. Guards are available in gray, yellow, black, blue, green, red, orange, purple and white.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Size
DP40-BB-(*)	\$5	1/8 DIN
DP116-BB-(*)	5	3/64 DIN

*Specify color code: “-GY” (gray), “-YL” (yellow), “-BK” (black), “-BL” (blue), “-GR” (green), “-RD” (red), “-OR” (orange), “-VL” (purple) or “-WH” (white).

Ordering Example: DP40-BB-YL, yellow protective guard for 1/8 DIN meters, \$5.

PATENTED

Covered by U.S and International patents and pending applications



SPC18, \$30

SPC14, \$30

SPC116-S, \$30

SPC364, \$30

SPC116-R, 30

**Tilt Bench Stand
DP41-TBS
(DP41 Series Only)**
\$25

DP41-TC, thermocouple thermometer, \$595. See page M-41 for details.



KMTXL-125G-6 thermocouple probe, \$27 (sold separately). See page A-45 for details.

Convert Your DP41 High-Performance Panel Meter into a Benchtop Meter!

Economical Tilt Bench Stand

The DP41-TBS allows the DP41 to be used as a benchtop meter at fixed angles, or it can act as a carrying handle to facilitate moving the meter.

Splash-Proof Covers

Splash-proof covers provide additional protection for instruments. Following NEMA 4 (IP66) guidelines for windblown dust and rain, splashing water and hose-directed water, SPC covers form a protective seal around the instrument bezel. Available in 1/4, 1/8, 1/16 and 3/64 DIN sizes for compatibility with most panel meters.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Size
SPC364	\$30	3/64 DIN cover (DP116 & DPF50 Series)
SPC116-S	30	For 1/16 DIN square cover
SPC116-R	30	For 1/16 DIN rectangular cover
SPC14	30	1/4 DIN cover, spring-clip-mounted
SPC18	30	1/8 DIN cover, spring-clip-mounted
SPC4	30	1/8 DIN cover, thumb-screw-mounted
DPP-2	425	3/64 DIN panel punch
DPP-4	475	1/16 DIN square panel punch
DPP-5	525	1/8 DIN panel punch

Ordering Examples: SPC116-S splash-proof cover for 1/16 DIN square meters, \$30. DPP-5, panel punch for 1/8 DIN cut out, \$525.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters