

# Heavy Duty Probes

- ✓ Each Probe Comes Standard with SMPW Miniature Connector
- ✓ Six Rugged Probe Styles Available in J, K and E Calibrations



- ✓ 1.8 m (6') PFA Coated 22 AWG Stranded Lead Wires
- ✓ Beaded Wire Probe Has Glass-on-Glass Insulation with Stainless Steel Overbraid [1.8 m (6')]

- ✓ Optional Extension Handle with 100, 300, 600 mm (4, 12 or 24") L
- ✓ Black Anodized Aluminum Handle on Handle Probes



**PATENTED**  
Covered by U.S. and International patents and pending applications.

Discount Schedule		
1-10 Units	.....Net 100 -499	.....30%
11-24 Units	....10% 500 and up	.....25%
25-99 Units	...20%	

**Also Available**  
Probes trimmed to 3.85 Ω  
For use with analog pyrometers that require 3.85 Ω lead resistance, the SP series heavy duty probes are available with lead lengths trimmed to 3.85 Ω. To order, change the 6 in the model number to 3.85. No additional price.

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)			
Code	Model No.	Price	Description
A	SP-RL-(*)-6	\$73	Curved surface probe
B	SP-GP(*)-6	61	General purpose probe
C	SP-BW-(*)-6	19	Beaded wire probe
D	SP-EH-4	22	100 mm (4") extension handle
	SP-EH-12	22	300 mm (12") extension handle
	SP-EH-24	22	600 mm (24") extension handle
E	SP-RA-(*)-6	80	Right angle probe
F	SP-SP-(*)-6	73	Surface probe
G	SP-NP-(*)-6	61	Needle probe

\* Specify calibration: J, K, or E.  
Ordering Example: SP-SP-J-6, Type J surface probe, with SMP connector, \$73.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters