

Specialty Thermocouple Probes

Low-Profile Penetration Probe

Model 88310(*)

\$50

*Specify calibration: K or E

6.4 mm (0.25")

MEETS OR EXCEEDS
SPECIAL LIMITS
OF ERROR (SLE)
AND EN 60584-2:
Tolerance Class 1

MADE IN
USA



This probe features a low-profile hypodermic tip and convenient handle for short depth penetration of soft materials such as rubber. A grounded junction, 300 mm (1') of retractable cable (which stretches to 1.5 m [5']) and a subminiature male connector are standard. The handle is rated to 162°C (325°F).

Molded Miniature Connector Shown smaller than actual size

Autoclave Probe

This 1.6 mm (0.063") diameter 304SS probe, with stainless steel transition junction, is perfect for the food industry, steam washdown applications or general heavy duty use. It features 3.3 m (11') of 1.6 mm (0.062") mineral insulated coiled cable, 1 m (3') of Teflon® insulated thermocouple grade wire and a male subminiature connector.

TJ36-(*)-116G-6-ACL

\$92

Grounded Junction

*Specify calibration: J, K, T or E

TJ36-(*)-116U-6-ACL


\$92

Ungrounded Junction

6.4 mm (0.25") dia.

Shown smaller than actual size

100 mm (4")



Miniature Connector

6.4 mm (0.25") dia.

Coil can be stretched or compressed by hand

Epoxy Coated Tip Thermocouple

TC-PVC-(*)-24-180

\$16 each


Miniature Connector With Write-On-Window

Purchase PVC insulated thermocouples with epoxy sealed junction tip either singly or in a pack of five. Supplied in 4.5 m (15') lengths† per sensor with subminiature male window connector and 24 gage solid polyvinyl rip-cord wire. Maximum Temp rating of 105°C (221°F). Stripped leads available at \$40/5-pack.

5TC-PVC-(*)-24-180

\$50
pkg of 5

*Specify calibration: J, K, T or E



Shown smaller than actual size

All probes were designed for industrial, laboratory, manufacturing and chemical research only. They are not intended for medicinal use, or on humans. OMEGA Engineering, Inc. assumes no responsibility if these products are used for medicinal purposes, or on humans, or are misused in any way.

†Other lengths available, consult Sales Department



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters