

Force/Strain Calibration Services Provided by OMEGADYNE®



- ✓ NIST Traceable Calibrations
- ✓ Reliable, Accurate Certificates
- ✓ Sensor Calibration, Meter Calibration and System Calibration Available
- ✓ High Capacity Dead Weight and Hydraulic Testers



“S” type load cell shown with DP41-S pressure indicator (\$545). See OMEGA’s pressure handbook for our complete line of pressure sensors, transducers, load cells, strain gages, instrumentation and pressure calibration equipment.



OMEGADYNE®, located in Columbus, Ohio maintains in-house state-of-the-art NIST traceable calibration standards for all your load cell and strain gage calibration needs. Pictured above is a high capacity dead weight tester (left) and hydraulic tester (right).



To Order (Specify Calibration Level)		
Cal Level	Price	Description
CAL-1	\$ 0	Statement of Conformance. (Must be requested at time of purchase).
CAL-2*	0	Statement of Traceability, no data points. (Must be requested at time of purchase).
CAL-3-FORCE	150	Calibration traceable to NIST with 5 data points (0%, 50%, 100% increasing, 50%, 0% decreasing)
CAL-4-FORCE	150 + 25/PT	Same as CAL-3 above plus the addition of customer selected data points.

*Not all products are available with NIST traceability
Note: Because of the large selection of load cells and pressure instrumentation OMEGADYNE and OMEGA offer, the pricing and calibration data points shown above are only an example and do not apply to every calibration. Contact OMEGADYNE’s or OMEGA’s Customer Service (1-800-622-BEST) prior to returning any instrument for calibration service.
Ordering Example: CAL-3-FORCE, designate this calibration level when NIST traceability is required on the load cell or strain gage you are purchasing new or returning previously purchased equipment for calibration, \$150.

For Calibration Services Call:

1-800-872-3963®
1-800-USA-DYNE

or

1-800-622-2378®
1-800-622-BEST