

RTD Temperature vs. Resistance Table

For American Curve, Alpha = .00392

1° Celsius Increments

°C	Ohms	°C	Ohms	°C	Ohms	°C	Ohms	°C	Ohms	°C	Ohms	°C	Ohms	°C	Ohms	°C	Ohms
-100	59.57	-38	84.80	24	109.51	86	133.75	148	157.53	210	180.86	272	203.74	334	226.17	396	248.16
-99	59.98	-37	85.20	25	109.90	87	134.14	149	157.91	211	181.23	273	204.11	335	226.53	397	248.51
-98	60.39	-36	85.60	26	110.30	88	134.52	150	158.29	212	181.61	274	204.47	336	226.89	398	248.86
-97	60.80	-35	86.01	27	110.69	89	134.91	151	158.67	213	181.98	275	204.84	337	227.25	399	249.21
-96	61.21	-34	86.41	28	111.09	90	135.30	152	159.05	214	182.35	276	205.20	338	227.61	400	249.56
-95	61.63	-33	86.81	29	111.48	91	135.68	153	159.43	215	182.72	277	205.57	339	227.96	401	249.91
-94	62.04	-32	87.21	30	111.88	92	136.07	154	159.81	216	183.09	278	205.93	340	228.32	402	250.26
-93	62.45	-31	87.61	31	112.27	93	136.46	155	160.19	217	183.47	279	206.30	341	228.68	403	250.61
-92	62.86	-30	88.01	32	112.66	94	136.84	156	160.57	218	183.84	280	206.66	342	229.04	404	250.96
-91	63.27	-29	88.42	33	113.06	95	137.23	157	160.95	219	184.21	281	207.02	343	229.39	405	251.31
-90	63.68	-28	88.82	34	113.45	96	137.62	158	161.33	220	184.58	282	207.39	344	229.75	406	251.66
-89	64.09	-27	89.22	35	113.84	97	138.00	159	161.70	221	184.95	283	207.75	345	230.11	407	252.01
-88	64.50	-26	89.62	36	114.24	98	138.39	160	162.08	222	185.32	284	208.12	346	230.46	408	252.36
-87	64.91	-25	90.02	37	114.63	99	138.77	161	162.46	223	185.70	285	208.48	347	230.82	409	252.71
-86	65.32	-24	90.42	38	115.02	100	139.16	162	162.84	224	186.07	286	208.85	348	231.18	410	253.06
-85	65.73	-23	90.82	39	115.42	101	139.55	163	163.22	225	186.44	287	209.21	349	231.53	411	253.41
-84	66.14	-22	91.22	40	115.81	102	139.93	164	163.60	226	186.81	288	209.57	350	231.89	412	253.76
-83	66.55	-21	91.62	41	116.20	103	140.32	165	163.97	227	187.18	289	209.94	351	232.25	413	254.11
-82	66.96	-20	92.02	42	116.59	104	140.70	166	164.35	228	187.55	290	210.30	352	232.60	414	254.46
-81	67.36	-19	92.42	43	116.99	105	141.09	167	164.73	229	187.92	291	210.66	353	232.96	415	254.80
-80	67.77	-18	92.82	44	117.38	106	141.47	168	165.11	230	188.29	292	211.03	354	233.31	416	255.15
-79	68.18	-17	93.22	45	117.77	107	141.86	169	165.48	231	188.66	293	211.39	355	233.67	417	255.50
-78	68.59	-16	93.62	46	118.16	108	142.24	170	165.86	232	189.03	294	211.75	356	234.03	418	255.85
-77	69.00	-15	94.02	47	118.56	109	142.63	171	166.24	233	189.40	295	212.11	357	234.38	419	256.20
-76	69.41	-14	94.42	48	118.95	110	143.01	172	166.62	234	189.77	296	212.48	358	234.74	420	256.55
-75	69.81	-13	94.82	49	119.34	111	143.39	173	166.99	235	190.14	297	212.84	359	235.09	421	256.89
-74	70.22	-12	95.22	50	119.73	112	143.78	174	167.37	236	190.51	298	213.20	360	235.45	422	257.24
-73	70.63	-11	95.62	51	120.12	113	144.16	175	167.75	237	190.88	299	213.56	361	235.80	423	257.59
-72	71.04	-10	96.02	52	120.51	114	144.55	176	168.12	238	191.25	300	213.93	362	236.16	424	257.94
-71	71.44	-9	96.42	53	120.91	115	144.93	177	168.50	239	191.62	301	214.29	363	236.51	425	258.29
-70	71.85	-8	96.81	54	121.30	116	145.31	178	168.88	240	191.99	302	214.65	364	236.87	426	258.63
-69	72.26	-7	97.21	55	121.69	117	145.70	179	169.25	241	192.36	303	215.01	365	237.22	427	258.98
-68	72.66	-6	97.61	56	122.08	118	146.08	180	169.63	242	192.73	304	215.37	366	237.58	428	259.33
-67	73.07	-5	98.01	57	122.47	119	146.47	181	170.00	243	193.09	305	215.74	367	237.93	429	259.67
-66	73.48	-4	98.41	58	122.86	120	146.85	182	170.38	244	193.46	306	216.10	368	238.28	430	260.02
-65	73.88	-3	98.81	59	123.25	121	147.23	183	170.76	245	193.83	307	216.46	369	238.64	431	260.37
-64	74.29	-2	99.20	60	123.64	122	147.61	184	171.13	246	194.20	308	216.82	370	238.99	432	260.72
-63	74.70	-1	99.60	61	124.03	123	148.00	185	171.51	247	194.57	309	217.18	371	239.35	433	261.06
-62	75.10	0	100.00	62	124.42	124	148.38	186	171.88	248	194.94	310	217.54	372	239.70	434	261.41
-61	75.51	1	100.40	63	124.81	125	148.76	187	172.26	249	195.31	311	217.90	373	240.05	435	261.75
-60	75.91	2	100.80	64	125.20	126	149.15	188	172.63	250	195.67	312	218.26	374	240.41	436	262.10
-59	76.32	3	101.19	65	125.59	127	149.53	189	173.01	251	196.04	313	218.63	375	240.76	437	262.45
-58	76.72	4	101.59	66	125.98	128	149.91	190	173.38	252	196.41	314	218.99	376	241.11	438	262.79
-57	77.13	5	101.99	67	126.37	129	150.29	191	173.76	253	196.78	315	219.35	377	241.47	439	263.14
-56	77.53	6	102.38	68	126.76	130	150.67	192	174.13	254	197.14	316	219.71	378	241.82	440	263.49
-55	77.94	7	102.78	69	127.15	131	151.06	193	174.51	255	197.51	317	220.07	379	242.17	441	263.83
-54	78.34	8	103.18	70	127.54	132	151.44	194	174.88	256	197.88	318	220.43	380	242.53	442	264.18
-53	78.75	9	103.57	71	127.93	133	151.82	195	175.26	257	198.25	319	220.79	381	242.88	443	264.52
-52	79.15	10	103.97	72	128.32	134	152.20	196	175.63	258	198.61	320	221.15	382	243.23	444	264.87
-51	79.56	11	104.37	73	128.71	135	152.58	197	176.01	259	198.98	321	221.51	383	243.58	445	265.21
-50	79.96	12	104.76	74	129.09	136	152.96	198	176.38	260	199.35	322	221.87	384	243.94	446	265.56
-49	80.36	13	105.16	75	129.48	137	153.35	199	176.75	261	199.71	323	222.23	385	244.29	447	265.90
-48	80.77	14	105.56	76	129.87	138	153.73	200	177.13	262	200.08	324	222.59	386	244.64	448	266.25
-47	81.17	15	105.95	77	130.26	139	154.11	201	177.50	263	200.45	325	222.94	387	244.99	449	266.59
-46	81.58	16	106.35	78	130.65	140	154.49	202	177.88	264	200.81	326	223.30	388	245.35	450	266.94
-45	81.98	17	106.74	79	131.04	141	154.87	203	178.25	265	201.18	327	223.66	389	245.70	451	267.28
-44	82.38	18	107.14	80	131.42	142	155.25	204	178.62	266	201.55	328	224.02	390	246.05	452	267.63
-43	82.79	19	107.53	81	131.81	143	155.63	205	179.00	267	201.91	329	224.38	391	246.40	453	267.97
-42	83.19	20	107.93	82	132.20	144	156.01	206	179.37	268	202.28	330	224.74	392	246.75	454	268.31
-41	83.59	21	108.32	83	132.59	145	156.39	207	179.74	269	202.64	331	225.10	393	247.10	455	268.66
-40	83.99	22	108.72	84	132.98	146	156.77	208	180.12	270	203.01	332	225.46	394	247.46	456	269.00
-39	84.40	23	109.11	85	133.36	147	157.15	209	180.49	271	203.38	333	225.81	395	247.81	457	269.35



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters