

PANEL MOUNT 40 AMP AA RELAY




9575H3A000
\$71



- DPDT 40 A Contacts
- Convenient Panel Mount
- Ideal for Controlling Small Motors

The 9575H3A000 is a Type AA DPDT relay with contacts rated (each pole) 40 A up to 300 Vac 50/60 Hz. The 9575H3A000 is panel mountable and ideal for applications when controlling smaller loads such as single-phase motors.

9575H3A000, \$71, shown close to actual size.



SPECIFICATIONS

Nominal Coil Voltage: 120 Vac 50/60 Hz

Coil Pull-In Voltage: 85% of nominal voltage or less @ 25°C

Coil Dropout Voltage: 10% of nominal voltage or more @ 25°C

Coil Resistance: ±10% measured @ 25°C

Pick Up Time (Average): 40 mS

Drop Out Time (Average): 35 mS

Contact Combination: DPDT

Contact Rating Each Pole (Main Contacts): Each pole rated 40 A up to 300 Vac, 50/60 Hz, 5 A @ 480/600 Vac 50/60 Hz, 0.75 pF inductive load; 1½ hp motor load (each pole) @ 120 thru 600 Vac 50/60 Hz; hp motor load @ 200 thru 600 Vac, 50/60 Hz only when using both poles to switch both sides of load, 40 A @ 28 Vdc resistive load each pole; NEMA A 600 pilot duty 50/60 Hz

Contact Material: Silver cadmium oxide, gold flashed; 7.9 mm (5/16") diameter standard


Dielectric Withstanding Voltage Between Open Contacts: 1500 Vrms

Dielectric Withstanding Voltage Between All Other Mutually Insulated Conductive Elements: 2200 Vrms

Coil Terminals: 6-32 binder head screws
Contact Terminals: 8-32 binder head screws

Main Base Material: Molded phenolic, UL recognized (QMFZ2)

Weight: 311 g (11 oz) approximately



To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	PRICE	DESCRIPTION
9575H3A000	\$71	DPDT type AA 120 Vac, 40 A relay

Comes complete with installation instructions.

Ordering Example: 9575H3A000, DPDT type AA 120 Vac, 40 A relay, \$71.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters