



Economical pH, ORP, Conductivity and TDS Testers

CDH-5021
\$46



- ✓ Economical
- ✓ Easy-to-Use
- ✓ Electrode Extends to 80 mm (3.1")

The CDH-5021, CDH-5022, PHH-5012, ORP-5041 and TDH-5031 are easy to use. These units feature a telescoping electrode which extends to 80 mm (3.1"). These kits are supplied with a carrying case, battery, calibration solution, and complete instructions.


CDH-5021, \$46.

TDH-5031, \$46.

OMEGAETTE™—Moderately Priced Instruments. Ideal for Education, Training and Demonstration Programs.

PHH-5012, \$50.

Pull-Out Telescoping Electrodes!



All products shown smaller than actual size. Carrying case, battery, screw driver, calibration solution and operation instructions included. **ORP-5041, \$85.**

■ MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)					
Model No.	CDH-5021	CDH-5022	TDH-5031	PHH-5012	ORP-5041
Price	\$46	\$50	\$46	\$50	\$85
Range	10 to 9990 μ S/cm	0 to 999 μ S/cm	10 to 9990 ppm	0 to 14.0 pH	\pm 999 mV
Resolution	10 μ S/m	1 μ S/m	10 ppm	0.02 pH	1 mV
Accuracy	\pm 1%FS	\pm 1%FS	\pm 1%FS	\pm 0.01 pH @ 25°C	\pm 5%FS
ATC	Yes (0 to 50°C)	Yes (0 to 50°C)	Yes (0 to 50°C)	Yes (0 to 50°C)	No
Power (Battery, included)	9V	9V	9V	3 required 1.55V	9V
Size	Meter: 152 x 40 x 34 mm (6 x 1.6 x 1.3"); carrying case: 165 x 100 x 40 mm (6.5 x 3.9 x 1.6")				
Weight	120 g (4.2 oz) with battery (avg)				

Accessories

Model No.	Price	Description
PH-BATT-3	\$3	1.55V replacement battery for PHH-5012, requires 3.
MN1604	3	9V replacement battery for CDH-5021, CDH-5022, TDH-5031, ORP-5041, requires 1.

Comes complete with carrying case, battery, screwdriver, calibration solution and operator's manual. ORP-5041 supplied with carrying case, battery, and operator's manual

Ordering Examples: PHH-5012, pH tester, \$50. ORP-5041, ORP tester, \$85.

Order Online
omega.com[®]
Over 100,000 Products Available!

To download information and to order pH Field and Lab Instrument products online, visit **omega.com**



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters