

# General Purpose Miniature Probes with **Miniature** Connector



Miniature connector standard.

Shown smaller than actual size.

- ✓ Works Great with Handheld Instruments
- ✓ 150 mm (6") Length Standard†
- ✓ 3.2 mm (1/8") OD 304 Stainless Steel Sheath
- ✓ Molded Junction Rated to 220°C (425°F)
- ✓ Color-Coded to Calibration
- ✓ 300 mm (12") Retractable Cable Expands to 1.2 m (48")
- ✓ SMPW Male Connector Termination
- ✓ Grounded Junction



The molded miniature probe conveniently plugs directly in to most handheld thermocouple meters. The color-coded retractable cable will stretch from 300 mm (12") to 1.2 m (48"). Ideal for use with handheld meters, the grounded junction probes are also suited for applications with benchtop meters and with oscillating machines. Available in calibration codes J, K, T and E.

**Very Popular System Shown!**



KTSS-HH probe with the HH11B handheld digital thermometer, \$74. Please visit [omega.com/hh11b](http://omega.com/hh11b) for complete details.

**Most Popular Models Highlighted!**

To Order (Specify Model Number)			
Thermocouple Alloy		Model No. ANSI Color Code	Price
Iron-Constantan	J	JTSS-HH	\$29
CHROMEGA®-ALOMEGA®	K	KTSS-HH	29
CHROMEGA®-Constantan	E	ETSS-HH	29
Copper-Constantan	T	TTSS-HH	29

**Note:** Hot end junction grounded.

† Other lengths are available, consult Sales Department

**Ordering Example:** KTSS-HH is a Type K thermocouple probe, 150 mm (6") long, 3.2 mm (1/8") dia with 1' of RSC cable (which stretches to 5') with a molded, miniature male thermocouple connectors, \$29.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters