


Special Purpose Probes

Dual Thermocouple Probe with NPT Fitting

1/8" NPT SS fitting for installation into any standard pipe opening. Dual sensors with 1 m (40") leads and SMPW connectors.



Shown smaller than actual size.

Miniature Connector

TC-K-NPT-G-36-DUAL-SMPW-M

\$60

13 mm (0.5")**

AVAILABLE FOR FAST DELIVERY!



STS-2X
\$79

Shown smaller than actual size.

Miniature Connector

STS-2X, Solder Iron Measuring Module with Sensor Head Element

STS-H Replacement sensor, \$60.

To Order (Specify Model Number)		
Model Number	Price	Description
TC-(*)-NPT-G-36-DUAL-SMPW-M	\$60	Dual thermocouple 1/8" NPT
RTD-NPT-72-(+)-DUAL-MTP	115	Dual RTD 1/8" NPT
STS-2X	79	Solder iron module
FTP-(*)-2-SMP-M	120	Flow through probe


* Specify Type J, K, T, or E Thermocouple type † Specify "E" for 0.00385 or "A" for 0.00392 curve.
 ** Other lengths are available, consult Sales Department
 Ordering Example: FTP-K-2-SMP-M, Type K, flow through probe with 1/4" stainless steel fitting and SMPW write-on connector, \$120.

OMEGA® VIP Probes (Veterinary Implantation Probes)

OMEGA's VIP's are designed for continuous monitoring of animal rectal temperatures. Unique construction makes them flexible enough that they do not cause undue animal discomfort while inserted, yet they are rigid enough for proper insertion to prevent the animal from discharging the probe during the test period.



See Section W




VIP Series Starts at
\$80

Shown smaller than actual size.

For Complete Details Visit omega.com/vip_probes

Flow Through Sensor



Shown smaller than actual size.

Miniature connector.

FTP-K-2-SMP-M
\$120

FTP Probe

Specially made to measure temperature in a 6 mm (1/4") diameter tube; 51 mm (2") stem protects connector from extreme environment of the pipe. Use in uncontaminated fluids. 304 stainless steel probe with 6 mm (1/4") diameter compression fittings on input and output flow ports.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters