

DIN RAIL POWER SUPPLIES



DR Series
Starts at
\$120



DR-240-24V, \$225, shown smaller than actual size.

- Universal AC Input (85 to 264 Vac)
- DC Compatible Input (120 to 370 Vdc)
- Protections: Short Circuit/Overload/Over Voltage/Over Temperature
- Cooling By Free Air Convection
- UL 508 (Industrial Control Equipment) Approved
- CE Marked
- LED Indicator for Power On
- 100% Full Load Burn-In Test
- Built-In EMI Filter and Low Ripple Noise

The DR series of power supplies provides a reliable DC power source for any industrial control system. These economical and reliable power supplies for industrial devices (PLCs, stepper drives, sensors, switches) are designed for use in harsh industrial environments. Combining rugged, compact enclosures, incorporating all international standards and approvals, and offering short-circuit, over-load, over-voltage, and over-temperature protection, the DR series makes your power supply choice a simple one. These high quality power supplies have passed a 100% full load burn-in test, and are UL/CUL listed, TUV/CB certified, and CE marked. Models are available with output ratings from 75 to 240 W, with 24 Vdc output. Customers can choose from a full range of input voltages (85 to 264 Vac and 120 to 370 Vdc compatible) making the DR series unbeatable.



DR-120-24V, \$130, shown smaller than actual size.



SPECIFICATIONS

Nominal Output Voltage: 24V

Rated Output Current:

DR-75-24: 3.2 A

DR-120-24: 5.0 A

DR-240-24: 10.0 A

Rated Output Power:

DR-75-24: 76.8 W

DR-120-24: 120 W

DR-240-24: 240 W

Efficiency (Typical):

DR-75-24: 80%

DR-120-24, DR-240-24: 84%

Input Voltage Range:

DR-75-24, DR-240-24:

85 to 264 Vac (47 to 63 Hz) or

120 to 370 Vdc

DR-120-24: 88 to 132 Vac/

176 to 364 Vac (by switch)

(47 to 63 Hz) or 248 to 370 Vdc

Input Current (Typical):

DR-75-24: 1.6 A @ 115V,

0.96 A @ 230V

DR-120-24: 2.6 A @ 115V,

1.6 A @ 230V

DR-240-24: 2.8 A @ 115V,

1.4 A @ 230V

Inrush Current (Typical):

DR-75-24: 20 A @ 115 Vac,

40 A @ 230 Vac, cold start

DR-120-24: 20 A @ 115 Vac,

40 A @ 230 Vac, cold start

DR-240-24: 27 A @ 115 Vac,

45 A @ 230 Vac, cold start

Output Voltage Range: 24 to 28V

Ripple and Noise:

DR-75-24: 150 mV p-p

DR-120-24, DR-240-24: 80 mV p-p

Line Regulation: 0.5%

Load Regulation: 1.0%

Temperature Coefficient: 0.03%/°C
(0 to 50°C)

Over Load Protection: 105 to 150%
rated output power, constant current
limiting, auto recovery

Over Voltage Protection:

DR-75-24: 121 to 141% rated
output voltage

DR-120-24: 120 to 140% rated
output voltage

DR-240-24: 30 to 36V

Over Temp Protection:

DR-75-24: 85°C, ±5°C

DR-120-24: 90°C, ±5°C

DR-240-24: 100°C, ±5°C

Hold-Up Time (Typical):

DR-75-24: 60 ms/230 Vac, 12 ms/
115 Vac at full load

DR-120-24: 36 ms/230 Vac, 32 ms/
115 Vac at full load

DR-240-24: 24 ms/230 Vac, 24 ms/
115 Vac at full load



DR-240-24V, \$225, shown smaller than actual size.

Leakage Current:

DR-75-24: <1 mA @ 240 Vac

DR-120-24, DR-240-24: <3.5 mA @
240 Vac

Operating Temperature:

DR-75-24, DR-120-24: -10 to 60°C
(14 to 140°F)

DR-240-24: -10 to 70°C
(14 to 158°F)

Operating Humidity: 20 to 90% RH
(non-condensing)

Storage Temperature: -20 to 85°C
(-4 to 185°F)

Storage Humidity: 10 to 95% RH
(non-condensing)

Vibration: 10 to 500 Hz, 2G 10 min/
1 cycle, period for 60 min each along
X, Y, Z axes; mounting: compliance to
IEC60068-2-6

Safety:

DR-75-24: UL508, TUV EN60950-1
approved

DR-120-24, DR-240-24: UL508,
UL60950-1, TUV EN60950-1
approved

Withstand Voltage: I/P-O/P: 3K Vac,
I/P-FG: 1.5K Vac, O/P-FG: 0.5K Vac
(1 minute)

Isolation Resistance: I/P-O/P, I/P-FG,
O/P-FG: 100M Ω/500 Vdc

EMI: Compliance to EN55011, EN55022
(CISPR22) Class B

Harmonic Current: Compliance to
EN61000-3-2, -3

EMS Immunity: Compliance to
EN61000-4-2,3,4,5,6,8,11, ENV50204,
EN55024, EN61000-6-2 (EN50082-2),
heavy industry level, criteria A

Weight (Typical):

DR-75-24: 600 g (21.075 oz)

DR-120-24: 790 g (27.75 oz)

DR-240-24: 1200 g (42.33 oz)

Dimensions:

DR-75-24:
55.5 W x 125.2 H x 100 mm D
(2.185 x 4.93 x 3.94")

DR-120-24:
65.5 W x 125.2 H x 100 mm D
(2.58 x 4.93 x 3.94")

DR-240-24:
125.5 W x 125.2 H x 100 mm D
(4.94 x 4.93 x 3.94")

To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	PRICE	DESCRIPTION
DR-75-24V	\$120	DIN rail power supply, 24 Vdc, 3.125 A
DR-120-24V	130	DIN rail power supply, 24 Vdc, 5 A
DR-240-24V	225	DIN rail power supply, 24 Vdc, 10 A

Ordering Example: DR-75-24V, DIN rail power supply, 24 Vdc, 3.125 A, \$120.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters