

GENERAL PURPOSE COMPACT 4PDT "ICE CUBE" PLUG-IN RELAYS WITH ENHANCED FEATURES




D2PF Series
Starts at
\$12



* DPF series only when used
with D2PA6 socket

- Flag Indicator Shows Relay Status in Manual or Powered Condition
- Bi-Polar LED Status Lamp Allows for Reverse Polarity Applications
- Shows Coil ON or OFF Status
- Ideal in Low Light Conditions
- Color Coded Pushbutton Identifies: AC Coils with Red or DC Coils with Blue Pushbuttons and Allows for Manual Operation of Relay Without the Need for Coil Power
- Ideal for Field Service Personnel to Test Control Circuits
- Lock Down Door, When Activated, Holds Pushbutton and Contacts in the Operate Position-Excellent for Analyzing Circuit Problems
- Finger-Grip Cover Allows Operator to Remove Relays from Sockets More Easily than Conventional Relays
- White Plastic ID Tag/Write Label Used for Identification of Relays in Multi-Relay Circuits

The D2PF series relays are general purpose plug-in style relays. These 4PDT relays are extremely compact and are available with coil voltage of 24 Vdc and 120 Vac. The D2PF series offer a number of enhanced features including LED status lamp, push-to-test button for manual relay operation, a convenient finger grip for removing relays and a write-on label that can be used for identifying the relay in multiple relay circuits.



D2PF4AT1, \$12, shown smaller than actual size.

D2PA6-10PK, \$84/package of 10, or single units, shown close to actual size.

SPECIFICATIONS

[INDUCTIVE LOAD (P.F. = 1.0)]
Coil Pickup Voltage (Max): 85% AC; 80% DC (% of nominal)
Coil Drop Out Voltage (Min): 10% AC; 10% DC (% of nominal)
Coil Maximum Voltage: 110% of nominal
Coil Insulation System per UL Standard 1446: Class B, 130°C (266°F)
Contact Configuration: 4PDT
Rated Load: 120 Vac to 3 A, 277 Vac, 28 Vdc to 3 A
Maximum hp Ratings: 1/10 hp, 120 Vac, 1/10 hp, 277 Vac
Contact Material: Fine silver, gold diffused
Pilot Duty: B300
Utilization Category (IEC): AC-15

Min Permissible Load: 100 mA @ 5 Vdc or 0.5 W
Contact Resistance: 100 Milliohms max @ 6V, 1 A
Dielectric Strength Coil to Contacts: 1500 Vrms
Dielectric Strength Across Open Contacts: 1000 Vrms
Dielectric Strength Contacts to Frame: 1500 Vrms
Dielectric Strength Insulation Resistance: 100 MΩ min @ 500 Vdc
Operating Temperature: -40 to 70°C (-40 to 158°F)
Storage Temperature: -40 to 105°C (-40 to 221°F)
Electrical Life Expectancy at Rated Resistive Load: 200,000 operations
Mechanical Life Expectancy at No Load: 10 million operations
Approximate Weight: 37 g (0.081 lb)



D2PA6 SOCKET

SPECIFICATIONS

Socket Type: Screw terminal

Electrical Ratings: 10 A, 300V

Mounting Torque: 0.79 to 0.90 Nm
(7 to 8 in-lb)




Hook-Up Wire Range: 14 to 28 AWG
solid or stranded

Hold Down Clip: PQC-1342
(when used with D2PF4 relay)

COIL RESISTANCE

COIL VOLTAGE	Ω	MA*
24 Vdc	650	37
120 Vac	4430	10

* At 60 Hz for AC coils.



To Order (Specify Model Number)		
MODEL NO.	PRICE	DESCRIPTION
D2PF4AA	\$12	4PDT relay, 120 Vac coil voltage
D2PF4AT1	12	4PDT relay, 24 Vdc coil voltage
D2PA6-10PK	84	Screw terminal socket for D2PF4AA and D2PF4AT1 relays (requires PQC-1342 hold down clip), 10-pack
PQC-1342-10PK	6	Hold down clip for D2PA6 screw terminals, 10-pack
D2PF4-BC	12	Screw terminal socket and hold down clip for D2PF4AA and D2PF4AT1 relays

Ordering Example: Ten D2PF4AA relays, 1 D2PA6-10PK 10-pack of relay sockets and 1 PQC-1342-10PK and 10-pack of hold down clips, (\$12 x 10) + 84 + 6 = \$210.

AVAILABLE FOR FAST DELIVERY!



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters