




INDUCTIVE PROXIMITY SENSORS

HIGH PERFORMANCE E57 PREMIUM+ SERIES 12, 18 AND 30 mm DIAMETER

Starts at
\$69



E57LAL18T111E, \$77,
shown larger than
actual size.

E57SAL18A2, \$101,
shown larger than
actual size.

- 2-Wire, 3-Wire, DC, and AC/DC Multiple Range Sensor Models
- Manufactured to Take Physical and Environmental Abuse
- Designed with Stainless Steel Barrel and New Potting Compound for Robust, High Temperature, High Pressure Washdown, as Well as Intense Shock and Vibration Applications
- Unmatched High Noise Immunity Eliminates Problems Associated with Electrical Noise (All Models >20V/Meter)
- 360° Output Status Indicator is Visible from Any Angle and in Any Light Condition
- Resettable Short Circuit Protection and Reverse Polarity in Select Models
- Wide Temperature Range -25 to 70°C (-13 to 158°F) on Cable, Micro-Style Connections

The Cutler-Hammer® Premium+ Series inductive proximity sensors have improved sensing performance, product durability and selection. This improved line of sensors carries the Premium+ Series name because we have upgraded the design to a rugged stainless steel body, shock resistant front caps and impact absorbing potting compound. Also, the Premium+ Series line now includes a choice of AC/DC and DC-only, 12, 18 and 30 mm sensors with unmatched noise immunity of greater than 20V/meter.

SPECIFICATIONS E57 PREMIUM+ SERIES

	2-WIRE SENSORS AC/DC	3-WIRE DC SENSORS
Operating Voltage	20 to 240 Vac/Vdc	6 to 48 Vdc
Maximum Load Current	250 mA @ 25°C 200 mA @ 70°C	500 mA @ 6 to 30 Vdc
Switching Frequency	60 Hz	12 mm: 1000 Hz 18 mm: 800 Hz 30 mm: 500 Hz
Leakage Current	≤2.0 mA	≤100 µA
Voltage Drop	≤12V @ <10 mA ≤4V @ >25 mA	≤2.5V
Holding Current	5 mA min	—
Burden Current	—	≤10 mA
Protection	Resettable short circuit; overload protection	Auto reset
Switching Hysteresis	<15% rated sensing distance	
Repeat Accuracy	Shielded Models: <1% sensing distance; Unshielded and extended range: <3%	
Time Delay Before Availability	<200 mS	
COMMON SPECIFICATIONS		
Output Indicator LED	360° viewable LED	
Operating Temperature	-25 to 70°C (-13 to 158°F)	
Enclosure Ratings	NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)	
Shock	30 g, 11 mS per IEC 68-2-76	
Vibration	10 to 55 Hz, 1 mm amplitude	
Housing Material	Stainless steel; Polycarbonate end bells; Ryton® front ends	



To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

INDUCTIVE PROXIMITY SENSORS							
TYPE	MODEL NO.	PRICE	OPERATING VOLTAGE	SENSING RANGE (SN) mm (in)	SHIELDING	CONNECTION TYPE ¹	
2-WIRE SENSORS							
18 mm Dia End Sensing NO Output	E57SAL18A2	\$101	24 to 240 Vac 50/60 Hz ² 20 to 240 Vdc	5 (0.2)	Shielded	2 m (6') cable	
	E57SAL18A2SA	119				3-pin micro AC connector	
	E57SAL18A2E	101		8 (0.3)	Unshielded	2 m (6') cable	
	E57SAL18A2EA	119				3-pin micro AC connector	
30 mm Dia End Sensing NO Output	E57SAL30A2	102	24 to 240 Vac 50/60 Hz ² 20 to 240 Vdc	10 (0.4)	Shielded	2 m (6') cable	
	E57SAL30A2SA	116				3-pin micro AC connector	
	E57SAL30A2E	102		15 (0.6)	Unshielded	2 m (6') cable	
	E57SAL30A2EA	116				3-pin micro AC connector	
3-WIRE SENSORS							
12 mm Dia End Sensing NO Output	E57LAL12T110	\$69	6 to 48 Vdc	2 (0.08)	Shielded NPN	2 m (6') cable	
	E57LAL12T110SD	85				4-pin micro DC connector	
	E57LAL12T111	69			Shielded PNP	2 m (6') cable	
	E57LAL12T111SD	85				4-pin micro DC connector	
	E57LAL12T110E	69		4 (0.16)	Unshielded NPN	2 m (6') cable	
		E57LAL12T110ED				85	4-pin micro DC connector
		E57LAL12T111E			69	Unshielded PNP	2 m (6') cable
					E57LAL12T111ED		85
18 mm Dia End Sensing NO Output	E57LAL18T110	77	6 to 48 Vdc	5 (0.2)	Shielded NPN	2 m (6') cable	
	E57LAL18T110SD	96				4-pin micro DC connector	
	E57LAL18T111	77			Shielded PNP	2 m (6') cable	
		E57LAL18T111SD				96	4-pin micro DC connector
	E57LAL18T110E	77		8 (0.3)	Unshielded NPN	2 m (6') cable	
		E57LAL18T110ED				96	4-pin micro DC connector
		E57LAL18T111E			77	Unshielded PNP	2 m (6') cable
					E57LAL18T111ED		96
30 mm Dia End Sensing NO Output	E57LAL30T110	85	6 to 48 Vdc	10 (0.4)	Shielded NPN	2 m (6') cable	
	E57LAL30T110SD	98				4-pin micro DC connector	
	E57LAL30T111	85			Shielded PNP	2 m (6') cable	
		E57LAL30T111SD				98	4-pin micro DC connector
	E57LAL30T110E	85		15 (0.6)	Unshielded NPN	2 m (6') cable	
		E57LAL30T110ED				98	4-pin micro DC connector
		E57LAL30T111E			85	Unshielded PNP	2 m (6') cable
					E57LAL30T111ED		98

¹ For cable lengths longer than 2 m (6'), add the number of the desired length in meters to the end of the listed model number (for model numbers ending with a number, add an "S" and then the length). Example for a 5 m cable: **E57LAL12A2** becomes **E57LAL12A2S5**.

² Avoid wiring these AC/DC models in series as the sensors may not perform reliably. Contact OMEGA's Applications Engineering with questions.

Ordering Examples: **E57SAL18A2**, 18 mm (0.7") Dia end sensing proximity switch with NO output and 2 m (6') cable, **\$101**.

E57LAL18T110SD, 18 mm (0.7") diameter, end sensing proximity switch with NO output and 4-pin micro DC connector, **\$96**.

Optional Cable: **CSDS4A4CY2202**, 4-pin micro AC cable, 2 m (6') long, **\$20.50**.

Accessories


MODEL	PRICE	DESCRIPTION
CSAS3F3CY2202	\$21.75	AC cable, 3-pin, 3-wire, 22 AWG, 2 m (6') PVC jacket
CSDS4A4CY2202	20.50	DC cable, 4-pin, 4-wire, 22 AWG, 2 m (6') PVC jacket
E57KM12	9.90	Bracket for 12 mm tubular sensors
E57KM18	9.90	Bracket for 18 mm tubular sensors
E58KAM18B	20.75	Bracket, adjustable ball swivel for 18 mm tubular sensors
E57KM30	13.00	Bracket for 30 mm tubular sensors




Recommended Mounting Clearances

For unshielded standard range sensors, clearance must be provided around the sensor when mounting for reliable performance. ("Sn" is the sensing range of the sensor, "d" is the sensor diameter.)

TYPE	SHIELDING	a	b
Standard Range	Shielded	0	0
	Unshielded	0.5 d	0.5 Sn




Cable Models



STANDARD RANGE

Connector Models



STANDARD RANGE

SIZE	SHIELDING	DIMENSIONS: mm (in)				
		OVERALL LENGTH A	THREAD LENGTH B	C	NUT WIDTH D	THREAD SIZE E
2-WIRE AC/DC—CABLE MODELS						
18 mm	Shielded	64.5 (2.54)	50.9 (2.00)	—	24 (0.94)	M18 x 1
	Unshielded	64.5 (2.54)	44.4 (1.75)	7.0 (0.28)	24 (0.94)	M18 x 1
30 mm	Shielded	69.3 (2.72)	50.27 (1.98)	—	36 (1.41)	M30 x 1.5
	Unshielded	69.3 (2.72)	37.85 (1.49)	13.26 (0.52)	36 (1.41)	M30 x 1.5
2-WIRE AC/DC—CONNECTOR MODELS						
18 mm	Shielded	69.06 (2.72)	50.9 (2.00)	—	24 (0.94)	M18 x 1
	Unshielded	69.06 (2.72)	44.4 (1.75)	7.0 (0.28)	24 (0.94)	M18 x 1
30 mm	Shielded	73.8 (2.91)	50.27 (1.98)	—	36 (1.41)	M30 x 1.5
	Unshielded	73.8 (2.91)	37.85 (1.49)	13.26 (0.52)	36 (1.41)	M30 x 1.5
3-WIRE DC SENSORS—CABLE MODELS						
12 mm	Shielded	62.4 (2.46)	50.27 (1.98)	—	17 (0.67)	M12 x 1
	Unshielded	62.4 (2.46)	45.77 (1.80)	5 (0.20)	17 (0.67)	M12 x 1
18 mm	Shielded	64.5 (2.54)	50.9 (2.00)	—	24 (0.94)	M18 x 1
	Unshielded	64.5 (2.54)	44.4 (1.75)	7.0 (0.28)	24 (0.94)	M18 x 1
30 mm	Shielded	69.3 (2.73)	50.27 (1.98)	—	36 (1.41)	M30 x 1.5
	Unshielded	69.3 (2.73)	37.85 (1.49)	13.26 (0.52)	36 (1.41)	M30 x 1.5
3-WIRE DC SENSORS—MICRO-CONNECTOR MODELS						
12 mm	Shielded	68.7 (2.71)	50.27 (1.98)	—	17 (0.67)	M12 x 1
	Unshielded	68.7 (2.71)	45.77 (1.80)	5 (0.20)	17 (0.67)	M12 x 1
18 mm	Shielded	69.3 (2.73)	50.9 (2.00)	—	24 (0.94)	M18 x 1
	Unshielded	69.3 (2.73)	44.4 (1.75)	7.0 (0.28)	24 (0.94)	M18 x 1
30 mm	Shielded	74.1 (2.92)	50.27 (1.98)	—	36 (1.41)	M30 x 1.5
	Unshielded	74.1 (2.92)	37.85 (1.49)	13.26 (0.52)	36 (1.41)	M30 x 1.5



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters